

Dermatril® LR 742



APPLICATION

- › laboratory and operations
- › protection of products
- › chemical industry
- › medical technology
- › pharmaceutical industry
- › electronic industry
- › chip processing

QUALITIES AND ADVANTAGES

- › disposable protective glove
- › very good sensitivity
- › excellent wearing comfort
- › reduced perspiration due to special nitrile
- › improved grip by roughened fingertips
- › good chemical resistance

CHEMICAL PROTECTIVE GLOVES



Article no.	742
Name	Dermatril® LR 742
Material	nitrile
Description	long cuff, rolled edge, roughened fingertips, powderfree
Length (mm)	270 - 290
Total thickness (mm)	0,11 ± 0,03
Colour	blue
Size	7, 8, 9, 10, 11
Classification	category III
	EN374-1/Type B EN374-5 ISO14644-1
	KPT Virus clean room class 100



FEATURES

- › clean room packaging
- › free from natural latex
- › AQL < 0,65
- › resistant against a multitude of cytostatic drugs
- › glove surface free from silicone (lacquer indifference, test method automotive industry)
- › virus-resistant according to ASTM 1671:2007
- › suitable for clean rooms of ISO class 5 according to EN ISO 14644-1
- › This glove meets the requirements of EN 455.
- › This glove is a medical product according to guideline 93/42/EWG.
- › ion analysis according to IEST-RP-CC005.2, method is tested
- › corresponds to GMP class A and B

www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoen
 Am Kreuzacker 9
 36124 Eichenzell
 Germany
 Phone +49 6659 87-300
 Fax +49 6659 87-318

Honeywell