


Features

- NiCr-Ni "K" Type Thermocouples
- Max. operating temperature 1200°C
- Protection tube AISI310(DIN1.4841) Stainless Steel
- Sensor type DIN/IEC-584 "K" Type
- Cable type Fiber glass+Fiber glass+Braided
- Tube Diameter 3mm
- Immersion Length 100mm
- Cable Length 2meter

RS PRO Mineral Isolated Bayonet Sonda "K" Type Thermocouples

RS Stock No: 0350435



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet "K" Type Thermocouples Temperature Sensor

Diameter(M): 3mm

Immersion Length(L): 100mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	0 °C / +1200 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	"K" Type Thermocouples (DIN/IEC-584)
Protection tube material	AISI310 (DIN1.4841) Stainless Steel

Mechanical Specifications

Diameter (M)	3mm
Immersion Length (L)	100mm
Cable Length (K)	2m

Electrical Connection



Thermoelement Connections

