




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **6**
Centerline (Pitch): **2 mm [.079 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	6
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
Contact Type	Pin
Contact Base Material	Brass



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon 66
Centerline (Pitch)	2 mm [.079 in]
Housing Color	Natural

Dimensions

Connector Length	12.8 mm [.503 in] .14 in
PCB Thickness (Recommended)	1.19 – 1.6 mm, 1.57 mm
Wire Size	.05 – .15 mm ² , .12 – .35 mm ²

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant





China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 172782-5 LOW PROFILE MINI AMP-IN	 TE Part # 172781-4 LOW PROFILE MINI AMP-IN (AWG#30-#26)Y-TY	 TE Part # 172781-3 LOW PROFILE MINI AMP-IN (AWG#30-#26)X-TY	 TE Part # 172782-7 LOW PROFILE MINI AMP-IN
 TE Part # 172781-1 MINI AMP-IN TERM 30-26 PTPBR	 TE Part # 172781-2 MINI AMP IN	 TE Part # 8-172782-6 LOW PROFILE MINI AMP-IN	

Customers Also Bought



TE Part #174463-1
070 MULTILOCK 2P P

TE Part #350218-1
UMN PIN 20-14 .0126PTPBR

TE Part #5-963715-1
MQS0,63 Sn rec LL unseal. 0,5-0,75

TE Part #172890-5
5P 2MM MINI AMP-IN HDR HSG

TE Part #1801174-1
2W TAB HP CONNECTOR BLACK

TE Part #281934-2
SINGLE WIRE SEAL

Documents

Product Drawings

6P 2MM MINI AMP-IN HDR HSG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172890-6_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172890-6_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172890-6_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

172890-6

Housing, Plug, Wire-to-Board, 6 Position, 2 mm [.079 in] Centerline, Crimp, 1 Row,
Natural, Printed Circuit Board, Power & Signal



English