

Color: green

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

PCB terminal block, Nominal current: 4 A, Nom. voltage: 250 V, Pitch: 3.5 mm, Number of positions: 5, Connection method: Spring-cage connection, Mounting: Soldering, Conductor/PCB connection direction: 90 °,

TTYTYTYTY T

The figure shows a 10-position

### Why buy this product

version of the product

- Available as a PCB terminal block or as a plug
- Miniature connection terminal for solid conductors
- 3.5 mm pitch
- More user friendly thanks to direct plug-in technology with release button
- Potentials can be easily looped through thanks to the double connection



### Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	4 017918 169619
Weight per Piece (excluding packing)	1.73 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length	7 mm
Pitch	3.5 mm
Dimension a	14 mm
Pin dimensions	0,4 x 0,9 mm
Hole diameter	1 mm

General

Range of articles	FK-MPT 0,5/V
Insulating material group	Illa



## Technical data

#### General

Rated surge voltage (III/3)	2.5 kV	
Rated surge voltage (III/2)	2.5 kV	
Rated surge voltage (II/2)	2.5 kV	
Rated voltage (III/3)	160 V	
Rated voltage (III/2)	250 ∨	
Rated voltage (II/2)	250 V	
Connection in acc. with standard	EN-VDE	
Nominal current I <sub>N</sub>	4 A	
Nominal cross section	0.5 mm <sup>2</sup>	
Maximum load current	4 A (with 0.5 mm <sup>2</sup> conductor cross section)	
Insulating material	PBT	
Solder pin surface	Sn	
Inflammability class according to UL 94	V0	
Stripping length	6.5 mm	
Number of positions	5	

#### Connection data

Conductor cross section solid min.	0.12 mm <sup>2</sup>
Conductor cross section solid max.	0.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	20

## Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

## UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	34131203

17/02/2015 Page 2 / 5



## Classifications

#### UNSPSC

UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

## Approvals

Approvals

#### Approvals

UL Recognized / SEV / cUL Recognized / EAC / cULus Recognized

Ex Approvals

#### Approvals submitted

#### Approval details

	В	D
mm²/AWG/kcmil	28-20	28-20
Nominal current IN	4 A	4 A
Nominal voltage UN	300 V	300 V

SEV	
mm²/AWG/kcmil	0.5
Nominal current IN	3 A
Nominal voltage UN	160 V

cUL Recognized		
	В	D
mm²/AWG/kcmil	28-20	28-20
Nominal current IN	4 A	4 A
Nominal voltage UN	300 V	300 V

EAC

ſ



### Approvals

cULus Recognized 🔊 🔊

#### Accessories

Accessories

Printed circuit board housing

Base strip - FK-MPT 0,5/ 5-IC-3,5 - 1905379



Header, Nominal current: 3 A, Rated voltage (III/2): 250 V, Number of positions: 5, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The touch-protected basic strip, serves to accommodate the FK-MPT 0,5 PCB terminal block.

#### Base strip - FK-MPT 0,5/ 5-ICV-3,5 - 1905528



Header, Nominal current: 3 A, Rated voltage (III/2): 250 V, Number of positions: 5, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The touch-protected basic strip, serves to accommodate the FK-MPT 0,5 PCB terminal block.

#### Screwdriver tools

Screwdriver - SZF 0-0,4X2,5 - 1204504



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

#### Additional products

Base strip - FK-MPT 0,5/ 5-IC-3,5 - 1905379



Header, Nominal current: 3 A, Rated voltage (III/2): 250 V, Number of positions: 5, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The touch-protected basic strip, serves to accommodate the FK-MPT 0,5 PCB terminal block.




### Accessories

Base strip - FK-MPT 0,5/ 5-ICV-3,5 - 1905528



Header, Nominal current: 3 A, Rated voltage (III/2): 250 V, Number of positions: 5, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The touch-protected basic strip, serves to accommodate the FK-MPT 0,5 PCB terminal block.

## Drawings



Phoenix Contact 2015 © - all rights reserved http://www.phoenixcontact.com