

## DCD996NT

# **18V XR Li-Ion Brushless Premium Hammer Drill Driver**

### **Selling Proposition**

- DEWALT's most powerful 18V XR Li-Ion Brushless XRP hammer drill driver
- NEW Automatic high speed hammer drill driver at 38,250 BPM increasing users masonry drilling speed of application
- NEW 3 Position LED torch, High/Medium/Low settings with High output 20min LED delay lighting up your work place
- Tough 3 speed all metal transmission for increased runtime and longer tool life
- Electronic Clutch with 11 position adjustable torque control for optimised precision when screw driving
- Includes a TSTAK Compatible Kitbox to organise you tools and accessory storage

### Standard Equipment

- Belt hook
- Magnetic bit holder
- Multi position side handle
- TSTAK heavy duty kitbox

### **Warranty Specifications**

• DEWALT 3 year European PT Guarantee (subject to registration)

| Specifications    |                           |
|-------------------|---------------------------|
| Battery chemistry | XR Li-Ion                 |
| Voltage           | 18 V                      |
| Max Torque (Hard) | 95 Nm                     |
| Max Torque (Soft) | 66 Nm                     |
| Power Output      | 820 Watt                  |
| No Load Speed     | 0-450/1300/2000 rpm       |
| Beats per Minute  | 0-8600/25500/38250<br>bpm |
| Chuck Capacity    | 1.5-13 mm                 |