

SATA III M.2 Solid State Drive M.2 SSD 800S

Transcend's SATA III 6Gb/s M.2 SSD 800S boasts ultra compact dimensions to address the high performance needs and strict size limitations of small form factor devices, best suited for Ultrabooks and thin, light notebooks. Featuring a powerful controller, exceptional transfer speeds, and MLC NAND flash memory, the M.2 SSD 800S easily handles everyday computing tasks as well as demanding multimedia applications, delivering steadfast reliability.




Perfect for your Ultrabook

Measured at just 80mm in length, the M.2 SSD 800S makes for an easy upgrade to your computer, taking up little space while giving it a much needed energy boost.



Superior transfer speeds

Transcend's M.2 SSD 800S reaches incredible read and write speeds of up to 500MB/s and 450MB/s. When used as a cache, the M.2 SSD 800S provides 1.5 times faster boot time than conventional hard drives.



Store more in less space

The M.2 form factor enables expansion and integration of functions onto a single form factor module solution. M.2 SSDs include a smaller form factor but with larger capacities than that of mSATA and half-slim SSDs.





SATA III M.2 Solid State Drive M.2 SSD 800S

Features

- · Space-saving M.2 Type 2280 form factor
- Up to 1TB storage capacity
- · Up to 500 MB/s read; 450 MB/s write
- MLC NAND flash memory and DDR3 DRAM cache
- Supports DevSleep ultra low power state, S.M.A.R.T., TRIM, and NCQ commands

Transcend

SSD Scope Software

Transcend SSD Scope is advanced, user-friendly software that makes it easy to ensure your Transcend SSD remains healthy, and continues to run fast and error-free by determining the condition and optimizing the performance of your drive.

Specifications

specifications			
Appearance			
Dimensions (Max.)	80.0 mm x 22.0 mm x 3.58 mm (3.15" x 0.87" x 0.14")		
Weight (Max.)	9 g (0.32 oz)		
Interface			
Bus Interface	SATA III 6Gb/s		
Storage			
Flash Type	MLC NAND flash		
Capacity	32 GB/64 GB/128 GB/256 GB/512 GB/1 TB		
Operating Environmen	t		
Operating Temperature	0°C (32°F) ~ 70°C (158°F)		
Operating Voltage	3.3V±5%		
Performance			
Sequential Read/Write	Read: 500 MB/s		
(ATTO, max.)	Write: 450 MB/s		
Sequential Read/Write	Read: 500 MB/s		
(CrystalDiskMark, max.)	Write: 430 MB/s		
4K Random Read/Write (IOmeter, max.)	Read: 70,000 IOPS		
	Write: 75,000 IOPS		
Mean Time Between Failures (MTBF)	1,500,000 hour(s)		
Terabytes Written (Max.)	2,360 TB		
Drive Writes Per Day (DWPD)	2 (3 yrs)		
Note			

Note

Speed may vary due to host hardware, software, usage, and storage capacity.

Warranty		
Certificate	CE/FCC/BSMI	
Warranty	Three-year Limited Warranty	

Ordering Information

32GB	TS32GMTS800S		
64GB	TS64GMTS800S		
128GB	TS128GMTS800S		
256GB	TS256GMTS800S		
512GB	TS512GMTS800S		
1TB	TS1TMTS800S		

Product specifications are subject to change without notice. Pictures shown may differ from actual products. When used as a storage capacity unit, one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.



SATA III M.2 SSDs Comparison					
	SATA III 6Gb/s M.2 SSD 400S	SATA III 6Gb/s M.2 SSD 600	SATA III 6Gb/s M.2 SSD 800S		
Appearance					
Dimensions (Max.)	42.0 mm x 22.0 mm x 3.58 mm (1.65" x 0.87" x 0.14")	60.0 mm x 22.0 mm x 3.58 mm (2.36" x 0.87" x 0.14")	80.0 mm x 22.0 mm x 3.58 mm (3.15" x 0.87" x 0.14")		
Weight (Max.)	5 g (0.18 oz)	7 g (0.25 oz)	9 g (0.32 oz)		
Storage					
Flash Type		MLC NAND flash			
Capacity	32GB ~ 512GB	32GB ~ 512GB	32GB ~ 1TB		
Operating Environment					
Operating Temperature	0°C (32°F) ~ 70°C (158°F)				
Performance					
Sequential Read/Write (ATTO, max.)	Read: 500 MB/s Write: 450 MB/s	Read: 550 MB/s Write: 460 MB/s	Read: 500 MB/s Write: 450 MB/s		
Sequential Read/Write (CrystalDiskMark, max.)	Read: 500 MB/s Write: 450 MB/s	Read: 520 MB/s Write: 460 MB/s	Read: 500 MB/s Write: 430 MB/s		
4K Random Read/Write (IOmeter, max.)	Read: 70,000 IOPS Write: 70,000 IOPS	Read: 75,000 IOPS Write: 75,000 IOPS	Read: 70,000 IOPS Write: 75,000 IOPS		
Mean Time Between Failures (MTBF)		1,500,000 hour(s)			
Terabytes Written (Max.)	1,100 TB	1,100 TB	2,360 TB		
Drive Writes Per Day (DWPD)		2 (3 yrs)			
Warranty					
Warranty	Three-year Limited Warranty				
Technology					
TRIM & NCQ Command	\checkmark	\checkmark	\checkmark		
S.M.A.R.T.	\checkmark	\checkmark	\checkmark		
DDR3 DRAM Cache	\checkmark	\checkmark	\checkmark		
Advanced Garbage Collection	\checkmark	\checkmark	\checkmark		
DevSleep Mode	\checkmark	\checkmark	\checkmark		
RAID Engine	-	-	-		
LDPC Coding	-	-	-		

 $\ensuremath{^*\text{Speed}}$ may vary due to host hardware, software, usage, and storage capacity.