


## FEATURES

- **Material Composition:** Constructed from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for enhanced chemical resistance
- **Temperature Range:** Operates effectively between -20 °C and 140 °C, suitable for diverse environments
- **Hardness:** Shore A 90 to 95 provides optimal flexibility and sealing capability
- **Dimensions:** Inside diameter of 26.65 mm and outside diameter of 31.89 mm for precise fitting
- **Compliance:** Meets standards such as BS ISO 3601-1, AS 568, and FDA, ensuring quality and safety

**RS PRO 26.65 mm O-Ring Seal, Shore A 90 to 95**

RS Stock No: 732-036



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in various industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures. Ideal for use in environments requiring robust sealing solutions, this O-Ring ensures durability and performance.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	26.65 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	31.89 mm
Thickness	2.62 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

