

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: BRASS

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A

-CONTACT RESISTANCE: ≤ 7.3 m ohms

-CONTACT/CONTACT : ≥ 1000 V

-CONTACT/GROUND : ≥ 1200 V

-INSULATION RESISTANCE: ≥ 5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 48 HOURS

MECHANICAL CHARACTERISTICS

RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.

- Termination plating spec:

Ni + Gold

- Active area plating spec:

Ni + Gold

- Shell plating :2 to 4µm Cu + Ni + 3 to 10µm Sn,pure bright

- Accessories: Sn pure bright + nickel

- Packaging spec: See GS-14-920

DBL13W3P043A00LF

Series

Shell size: **E A B C D**
see sheet 3

Front accessory definition
see sheet 2

Blank :without accessory

L :threaded insert M3

O :threaded insert UNC 4-40

Layout of contacts (see sheet 3)

Contacts

P :Pin

Plating

Blank signal solder bucket 200 matings/unmatings

043 signal solder bucket 500 matings/unmatings

PCB accessory definition



A without accessory on PCB

Power contacts

00 without power contact

See note RoHS

I3W3 FOR EXAMPLE



www.fciconnect.com				surface - ☒ tolerance std		projection		mm	
				ISO 1302		ISO 406 ISO 1101			
				TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr		M PESSON		2005-10-11		ANGULAR		size	
Eng		P LEGARE		2005-10-11		LINEAR		A2	
Chr						0.X		±0.3	
Apr						0.XX		±0.1	
18						0.XXX		±0.05	
				Product family		- Spec ref		ECN LS07-0273	
FCI		SUB MALE DW				C01-8639-2307		Re	
		mixed power+solder bucket				D		D	
catalog no						CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
A	LS05-0101	MPE	2005-10-11
B	LS06-0208	LGO	2006-12-13
C	LS07-0173	MPE	2007-06-18
D	LS07-0273	MPE	2007-10-31
-	-	-	-
-	-	-	-
-	-	-	-





FCI
SUB MALE DW
mixed power+solder bucket
catalog no


deg no
C01-8639-2307
Rev.
D
sheet 1 of 7





Copyright FCI.














www.fciconnect.com			surface  tolerance std		projection 		mm 		
			ISO 1302		ISO 406 ISO 1101				
TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	M PESSON	2005-10-11	ANGULAR	0.X	±0.3	size A2	Scale 2:1		
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	±0.1				
Chr			0° ±2°	0.XXX	±0.05				
Appr			Product family		ECN LS07-0273				
					- Spec ref				
FCI 			SUB MALE DW			C01-8639-2307		Rev. D	
mixed power+solder bucket			catalog no			CUSTOMER		sheet 7 of 7	