

SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676

<https://www.phoenixcontact.com/gb/products/1027676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, straight, M12-Push-pull external locking, coding: A, Rear mounting, M16, Wave soldering, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Established M12 standard for secure transmission of signals, data, and power
- Easy and quick cabling of devices and systems in hard-to-reach areas
- Manufacturer-independent M12 push-pull locking system for maximum availability
- Reliable shield connection even under extreme mechanical strain

Commercial data

Item number	1027676
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQCAA
Product key	ABQECJ
GTIN	4055626533926
Weight per piece (including packing)	17.53 g
Weight per piece (excluding packing)	16.185 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676

<https://www.phoenixcontact.com/gb/products/1027676>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting M16 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection	
Connection method	Wave soldering
Contact connection type	Pin

Mechanical properties

SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676

<https://www.phoenixcontact.com/gb/products/1027676>

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Head locking type	Push-pull external locking
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010
Note	Push-pull


SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting

1027676

<https://www.phoenixcontact.com/gb/products/1027676>

Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676
<https://www.phoenixcontact.com/gb/products/1027676>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1027676>

	cULus Recognized Approval ID: E221474-20140616			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676
<https://www.phoenixcontact.com/gb/products/1027676>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-MS-5CON-M16-L180 PP - Device connector rear mounting



1027676

<https://www.phoenixcontact.com/gb/products/1027676>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk