




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**
Housing Type: **Tab Housing**
Number of Positions: **6**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Product Type	Terminal Housing
Sealable	No
Housing Type	Tab Housing
Insulated	No

Configuration Features

Number of Positions	6
---------------------	---

Body Features

Number of Rows	2
Primary Product Color	White

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	Without



Mechanical Attachment

Mating Alignment	With
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polyamide 6.6 GF
Centerline (Pitch)	9.1 mm[.358 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 <p>TE Part # 926330-1 PL 250 REC HSG 6P NYLON BLACK</p>	 <p>TE Part # 926646-1 PL 250 REC HSG 8P NYLON BLACK</p>	 <p>TE Part # 179182-6 POSITIVE LOCK 187 (4.8 MM) HOUSING</p>	 <p>TE Part # 179182-1 POSITIVE LOCK 187 (4.8 MM) HOUSING</p>
 <p>TE Part # 179182-7 POSITIVE LOCK 187 (4.8 MM) HOUSING</p>	 <p>TE Part # 926330-3 6P POS-LOCK BU GEH</p>	 <p>TE Part # 926646-8 PL 250 8P HOUSING PA6.6 ZYTEL 101 WHITE</p>	 <p>TE Part # 1-1743103-1 2P PL 187 HOUSING TAB NATURAL 6 /6 NYLON</p>
 <p>TE Part # 926646-3 PL 250 8P HOUSING PA6.6 ZYTEL 101NATURAL</p>	 <p>TE Part # 926646-4 8P POS-LOCK GEH 6,3</p>		

Also in the Series | Positive Lock 250

 <p>Automotive Terminals(1)</p>	 <p>Crimp Terminal Housings(202)</p>	 <p>Insertion & Extraction Tools(3)</p>	 <p>Insulation Boots & Sleeves(4)</p>
--	--	--	--



Documents

Product Drawings

6P POS-LOCK BU GEH

English

CAD Files

Customer View Model

[ENG_CVM_CVM_926330-8_F.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_926330-8_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926330-8_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.