




Jobber Drill, Right Hand
DIN 338 RN / BS 328 /
ISO 235

Flute Geometry

Standard Helix, Right Hand Spiral,
 Wider Flutes

Point Angle

118°

Special Point Geometry
 (Dormer P.S.Point)

Giving Higher Positional Accuracy.

Surface Treatment

Blue flutes, Bronze lands & point

Application

General purpose engineering drills

New

d ₁ Øh8 inch	d ₁ Øh8 mm	l ₂ mm	l ₁ mm	d ₁ Øh8 inch	d ₁ Øh8 mm	l ₂ mm	l ₁ mm	d ₁ Øh8 inch	d ₁ Øh8 mm	l ₂ mm	l ₁ mm
1/8	3,00	33	61	1/4	6,35	63	101	25/64	9,80	87	133
	3,10	36	65		6,40	63	101		9,90	87	133
	3,18	36	65		6,50	63	101		9,92	87	133
	3,20	36	65		6,60	63	101		10,00	87	133
	3,25	36	65		6,70	63	101		10,10	87	133
	3,30	36	65		6,75	69	109		10,20	87	133
9/64	3,40	39	70	17/64	6,80	69	109	13/32	10,30	87	133
	3,50	39	70		6,90	69	109		10,32	87	133
	3,57	39	70		7,00	69	109		10,40	87	133
	3,60	39	70		7,10	69	109		10,50	87	133
	3,70	39	70		7,14	69	109		10,60	87	133
	3,80	43	75		7,20	69	109		10,70	94	142
5/32	3,90	43	75	9/32	7,30	69	109	27/64	10,72	94	142
	3,97	43	75		7,40	69	109		10,80	94	142
	4,00	43	75		7,50	69	109		10,90	94	142
	4,10	43	75		7,54	75	117		11,00	94	142
	4,20	43	75		7,60	75	117		11,10	94	142
	4,30	47	80		7,70	75	117		11,11	94	142
11/64	4,37	47	80	19/64	7,80	75	117	7/16	11,20	94	142
	4,40	47	80		7,90	75	117		11,30	94	142
	4,50	47	80		7,94	75	117		11,40	94	142
	4,60	47	80		8,00	75	117		11,50	94	142
	4,70	47	80		8,10	75	117		11,51	94	142
	4,76	52	86		8,20	75	117	29/64	11,60	94	142
3/16	4,80	52	86	5/16	8,30	75	117		11,70	94	142
	4,90	52	86		8,33	75	117		11,80	94	142
	5,00	52	86		8,40	75	117		11,90	101	151
	5,10	52	86		8,50	75	117		11,91	101	151
	5,16	52	86		8,60	81	125		12,00	101	151
	5,20	52	86		8,70	81	125	15/32	12,10	101	151
13/64	5,30	52	86	21/64	8,73	81	125		12,20	101	151
	5,40	57	93		8,80	81	125		12,30	101	151
	5,50	57	93		8,90	81	125		12,30	101	151
	5,56	57	93		9,00	81	125		12,40	101	151
	5,60	57	93		9,10	81	125		12,50	101	151
	5,70	57	93		9,13	81	125	31/64	12,60	101	151
7/32	5,80	57	93	23/64	9,20	81	125		12,70	101	151
	5,90	57	93		9,30	81	125		12,70	101	151
	5,95	57	93		9,40	81	125		12,80	101	151
	6,00	57	93		9,50	81	125		12,90	101	151
	6,10	63	101		9,53	87	133		13,00	101	151
	6,20	63	101	3/8	9,60	87	133	1/2			
15/64	6,30	63	101		9,70	87	133				