



MODULAR WORKBENCH SYSTEM

Configuration Guide

RANGE INTRODUCTION



Maximise productivity with the modular RS PRO workbench system. A robust and versatile system designed for demanding industrial, manufacturing, assembly, and maintenance environments. Featuring a durable 24 mm HEXA worktop, this workbench delivers the perfect combination of strength, organisation and flexibility. With a 350 kg load capacity, the heavy-duty steel construction provides exceptional stability for tools, equipment, and components, while the manual height adjustment allows users to create an ergonomic working position tailored to their needs. The extensive set of accessories allows to flexibly extend existing workbenches or easily customize the wanted combination right and start.

Whether used in workshops, production facilities, laboratories, or maintenance departments, the RS PRO workbench system is built to withstand everyday industrial use while creating a more organised, comfortable, and productive workspace

KEY FEATURES

- **Heavy-duty steel construction**
- **Durable 24 mm HEXA worktop**
- **Ergonomic manual height adjustment of 5 cm**
- **Maximum load capacity: 350 kg**
- **Large 2000 × 880 mm working area**
- **Ideal for industrial, assembly, maintenance, and workshop applications**

Get started with three basic types...



RS Stock No.	Product Description	Width	Depth	Height
800-806	RS PRO Workbench	2000	880	850
800-807	RS PRO Workbench with storage container	2000	880	850
800-808	RS PRO Workbench with storage container, back wall, power distribution unit (Schuko) and LED Lighting	2000	880	850


...ready for instant use or flexible customisation

Available accessories for flexible combination



WORKSTATION EXTENSIONS FOR PERFORATED BACK PANEL AND LIGHT HOLDER

RS Stock No.	Product Description
800-775	HIGH EXTENSION, 1980 x 1800mm
800-774	MEDIUM EXTENSION, 1980 x 1500mm
800-773	LOW EXTENSION, 1980 x 1100mm
800-776	MIDDLE VERTICAL UPRIGHT, 40 x 1800mm (use only with 800-775)



PERFORATED BACK PANELS

RS Stock No.	Product Description
800-839	FULL WIDTH LOW, 2000 x 300mm
800-840	FULL WIDTH HIGH, 2000 x 600mm
800-830	1/2 WIDTH LOW, 1000 x 300mm (use vertical upright 800-776)
800-831	1/2 WIDTH HIGH, 1000 x 600mm (use vertical upright 800-776)

Available accessories for flexible configuration



SHELVES – ½ WIDTH

(REQUIRE FULL WIDTH BACK PANEL OR VERICAL UPRIGHT 800-776)

RS Stock No.	Product Description
800-861	950 X 300 MM, ADJUSTABLE SHELF INCLINATION
800-862	990 X 300 MM
800-863	990 X 400 MM



SHELVES – FULL WIDTH

RS Stock No.	Product Description
800-875	1940 X 300 MM, ADJUSTABLE SHELF INCLINATION
800-876	1980 X 300 MM
800-877	1980 X 400 MM



KEYBOARD SHELF

(FOR MOUNTING UNDER WORKTOP)

RS Stock No.	Product Description
800-882	700 X 351 MM

Available accessories for flexible configuration



LIGHT HOLDER (REQUIRES WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-723	1950 x 340 MM (INCL. FRAME WITH RAILS FOR TOOL BALANCER CART 800-795)



LED LIGHT

RS Stock No.	Product Description
800-726	LED LIGHT TO FIT LIGHT HOLDER 800-723



TOOL BALANCER CART

RS Stock No.	Product Description
800-795	2 REQUIRED (FOR TOOL BALANCERS 793-2774, 793-2777 OR 793-2771)
800-667	BRAKE FOR CART – DIAMETER 25 MM



please order seperately

Available accessories for flexible configuration



SUSPENDED DRAWER UNITS

(FOR MOUNTING UNDER WORKTOP – MAX. 2 PER WORKSTATION)

RS Stock No.	Product Description
800-685	WITH 1 LOCKABLE DRAWER
800-687	WITH 1 LOCKABLE DRAWER – Silent Closing
800-688	WITH 2 LOCKABLE DRAWERS
800-689	WITH 2 LOCKABLE DRAWERS – Silent Closing
800-690	WITH 3 LOCKABLE DRAWERS
800-691	WITH 3 LOCKABLE DRAWERS – Silent Closing



DRAWER UNITS

(WITH CASTORS)

RS Stock No.	Product Description
800-682	WITH 4 LOCKABLE DRAWER
800-683	WITH 4 LOCKABLE DRAWER – Silent Closing

Available accessories for flexible configuration



POWER DISTRIBUTION UNITS (FOR USE WITH WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-848	1/2 WIDTH, 978 X 100 MM, 6 sockets – FRENCH (REQUIRE VERICAL UPRIGHT 800-776)
800-849	1/2 WIDTH, 978 X 100 MM, 8 sockets – SCHUKO (REQUIRE VERICAL UPRIGHT 800-776)
800-850	1/2 WIDTH, 978 X 100 MM, 6 sockets – FRENCH (REQUIRE VERICAL UPRIGHT 800-776)
800-851	1/2 WIDTH, 978 X 100 MM, 8 sockets – SCHUKO (REQUIRE VERICAL UPRIGHT 800-776)
800-732	FULL WIDTH, 1900 X 100 MM, 6 sockets – FRENCH
800-733	FULL WIDTH, 1900 X 100 MM, 8 sockets – SCHUKO
800-734	FULL WIDTH, 1900 X 100 MM, 6 sockets – FRENCH
800-735	FULL WIDTH, 1900 X 100 MM, 8 sockets – SCHUKO



BIN RAILS (FOR USE WITH WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-785	1/2 WIDTH BIN RAIL – 1000 MM (use vertical upright 800-776)
800-790	FULL WIDTH BIN RAIL – 2000 MM




FIND SUITABLE STORAGE BINS ON WWW.RS-ONLINE 

Available accessories for flexible configuration



FOOTREST

RS Stock No.	Product Description
800-693	600 x 360 MM



PC HOLDER

RS Stock No.	Product Description
800-829	225 x 463 MM




ARTICULATED KEYBOARD SHELF (USE WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-508	230 x 330 MM



DOCUMENT HOLDER (USE WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-684	FOR A4 DOCUMENTS



MONITOR HOLDER (USE WORKSTATION EXTENSION)

RS Stock No.	Product Description
800-728	55 x 120 MM