



Head protection

MEIA SMOKE

SAFETY GLASSES

Lightweight, one-piece, smoked-lens safety glasses with non-slip tips



Specific benefits



Comfort

· Contemporary wrap-around bifocal design offers a close fit and comfortable protection.



Easy to use

· Anti-slip ends for an increased comfort and very good hold on the head (or on a helmet)



Compatibility

· Extra flat temples for optimal comfort with Ear muffs



Benefits elements

· Ear protection compatibility

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Transportation
- Storage

Certifications and norms



EN172

UV 5 - 3.1

EN166

1 FT / FT

Protects against risks



UV / IR

enjoy safety



Head protection

MEIA SMOKE

SAFETY GLASSES

Lightweight, one-piece, smoked-lens safety glasses with non-slip tips

Standards - Details

Technical details

Use	Outside
Type of eye protection	Glasses
Lens matériel	Polycarbonate
Lens treatment	Anti-scratch (classic), UV400
Lens based curve	9.5
Lens support	Monobloc
Lens color	Smoke
Optical class	1
Lens protection class	3.1
Lens characteristic	Curved
Mechanical strength (lens)	F, T
Nose pad material	Polycarbonate
Frame material	Polycarbonate
Frame	Temples
Frame color	Black, Yellow
Mechanical strength (frame)	F, T
Temples benefit	Non-slip temples
Temples confort	Non-slip temples
Weight (g)	22








Head protection

MEIA SMOKE

SAFETY GLASSES

Lightweight, one-piece, smoked-lens safety glasses with non-slip tips

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
MEIAFU	Smoke	-	MEIA SMOKE	3295249194581	13295249194588	100	10	5.746 kg	30.6 cm	39.6 cm	53.4 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height