

6345 // ESD 3D CUT C

Cut protection gloves
PPE risk category II



Perfect and innovative fit thanks 3D FIT
18 Gauge
Antistatic (dissipative)

18
GAUGE



6345 // ESD 3D CUT C



Material:	Special yarn, anthracite
Coating:	Nitrile micro foam, black
Size(s):	6-12
Packaging unit:	100 pair(s)
Certification:	EN 388, OEKO-TEX STANDARD 100®

NITRAS ESD 3D CUT C, cut protection gloves, special yarn, anthrazit, integrated carbon fibre, nitrile micro foam coating, black (colour code: 1510), partly coated on palm and fingertips, high mechanical resistance, knitted wrist, high cut resistance, perfect dexterity, perfect and innovative fit thanks 3D FIT, unique comfort and protection for the user, 18 Gauge, reinforced thumb crotch, touchscreen capable, washable, premium quality, antistatic (dissipative), skin compatibility tested (dermatest®), for food contact, OEKO-TEX STANDARD 100®, ANSI A3 CUT, very slip resistant, perfect grip, very high abrasion resistance, very good dry and oil grip, PPE risk category II



EN ISO 21420

18
GAUGE



Size	6	7	8	9	10	11	12
Colour coding system							

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Wood processing

Advantages

- + Perfect and innovative fit thanks 3D FIT
- + 18 Gauge
- + Antistatic (dissipative)



Performance values

EN 16350:2014	Test parameter	Performance levels	Test result
	Palm (resistance in Ω)	-	$9,28 \times 10^6$ (dissipative)
	Back of the hand (resistance in Ω)	-	$7,68 \times 10^6$ (dissipative)
	Cuff (resistance in Ω)	-	$2,45 \times 10^6$ (dissipative)
EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 3X31C	Abrasion resistance	1-4	3
	Blade cut resistance (Coupe-Test)	1-5	X
	Tear resistance	1-4	3
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	C
EN ISO 21420:2020	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	Nitrile micro foam on special yarn	black
Index finger and thumb	Nitrile micro foam on special yarn	black
Back of the hand	Special yarn	anthracite
Fingertips	Nitrile micro foam on special yarn	black
Cuff / knitted wrist	Special yarn	anthracite



Washing cycles (max.) 5

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
6	4059904207011	4059904207080	0,54 m	0,3 m	0,24 m	4,59 kg	45
7	4059904207028	4059904207097	0,54 m	0,3 m	0,24 m	4,99 kg	45
8	4059904207035	4059904207103	0,54 m	0,3 m	0,24 m	5,19 kg	45
9	4059904207042	4059904207110	0,54 m	0,3 m	0,24 m	5,59 kg	45
10	4059904207059	4059904207127	0,54 m	0,3 m	0,24 m	5,99 kg	45
11	4059904207066	4059904207134	0,54 m	0,3 m	0,24 m	6,39 kg	45
12	4059904207073	4059904207141	0,54 m	0,3 m	0,24 m	6,79 kg	45

Customs tariff number: 61161020910

Country of origin: China