

Previously known as: MICROGARD® 1500 PLUS - Model 113

Comfortable protection from hazardous particulates in critical environments..

DESIGN

SMS fabrics are a particularly good barrier against particulates such as asbestos, brick dust and cement dust, and will provide protection from light aerosol mists; as found in some paint spray environments.

Anti-static suit, used for the stripping, clear up or handling of asbestos, general maintenance, construction and contract cleaning.

STITCHED SEAMS

Combining strength with particle barrier

SUIT FEATURES

- 3-piece hood
- Elasticated hood, wrists, waist and ankles
- 2-way front zipper with resealable storm flap
- Finger loops
- Anti-static treatment

SIZES

S-3XL



Industries

- Machinery and Equipment
- Life Sciences
- Metal fabrication
- Construction
- Chemical

Applications


- Unpacking of bulk goods
- Loading and unloading of process equipment
- Body Surface checking, marking and touching up
- Assembly & inspection of components
- Painting or cleaning tools or robots
- Production line support & maintenance

KEY FEATURES & BENEFITS

- Proven protection, filters 99.9% of particles >3 microns*
- Air and water vapour permeable (breathable) fabric helps reduce the risk of heat stress
- Optimised body fit, improving wearer comfort and safety
- Silicone free, critical in spray painting applications
- Anti-static, tested according to EN 1149-5

* KAKEN Particle penetration test

Material Diagram



Seam Diagram



Performance Standards



Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL
Color	Blue
Country Of Origin	China
Models Available	103,111
Packaging Overview	Individually packaged
Product Material	SMS fabric with anti-static treatment
Product Reference	1500 PLUS - Model 113
Standards Overview	CE CATEGORY III (Type 5, Type 6, EN 1073-2, EN 1149-5)
Seam Type	Stitched
Shelf Life	5 years
Style Number	B15S113

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall with 3-piece hood, 2-way front zipper with re-sealable storm flap and finger loops. Elasticated hood, wrists, waist and ankles. Reflective Hi-Vis tape for enhanced visibility.

For additional in formation visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

