



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**  
Ratchet Configuration: **Not Releasable, Not Adjustable**  
Die Sets Type: **Removable/Interchangeable**  
Specification Type: **TE Product Specification (114-)**  
Power Technology Type: **Manual**

Features

Other

|                       |                                 |
|-----------------------|---------------------------------|
| Tool Grade            | Commercial Crimp Tooling        |
| Ratchet Configuration | Not Releasable, Not Adjustable  |
| Die Sets Type         | Removable/Interchangeable       |
| Specification Type    | TE Product Specification (114-) |
| Power Technology Type | Manual                          |
| Tooling Type          | PRO-CRIMPER Hand Tool           |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |  |
|---|--|
| EU RoHS Directive 2011/65/EU                  | Compliant  |
| EU ELV Directive 2000/53/EC                   | Out of Scope   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free  |



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1596981-1  
[DIE SET ASSY](#)

Customers Also Bought

TE Part #CAT-D48-ST273  
[DEUTSCH Solid Contacts](#)

TE Part #DT04-2P  
[REC, 2P, GRY, N](#)

TE Part #DT06-2S  
[PLG, 2P, GRY, N](#)

TE Part #CAT-D487-W416  
[Wedgelocks: DEUTSCH DT](#)

TE Part #CAT-AM71-CH8172  
[AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING](#)

TE Part #281934-2  
[SINGLE WIRE SEAL](#)

TE Part #114017-ZZ  
[SEALING PLUG, SIZE 12/16, WHT](#)

Documents

[Product Drawings](#)  
[SHELL BARREL CRIMP TOOL](#)



Japanese

Datasheets & Catalog Pages  
1-1773865-2\_1015\_Commercial Manual Hand Tools

English  
Bottoming Dies  
English

Product Specifications  
SHELL BARREL CRIMP TOOL  
Japanese  
SHELL BARREL CRIMP TOOL  
Japanese