




Energy & Power > Solar Connectors & Adapters > SOLARLOK PV4-S DC Crimp Connectors



Solar Connector Type: **DC/AC Converter Receptacle**
Solar Connector Style: **Socket**
Contact Base Material: **Copper Alloy**
Keying Type: **Neutral**
Wire Size: **14 AWG**

[All SOLARLOK PV4-S DC Crimp Connectors \(12\)](#)

Features

Product Type Features

Solar Connector Type	DC/AC Converter Receptacle
Solar Connector Style	Socket

Configuration Features

Keying Type	Neutral
-------------	---------

Contact Features

Contact Plating Material	Tin
Contact Base Material	Copper Alloy

Housing Features

Housing Color	Black
Housing Material	Polycarbonate (PC)

Dimensions

Wire Size	2.5 mm²
-----------	---------



Industry Standards

IP Rating	IP68
Compatible With Agency/Standards Products	UL

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1971920-2
SOCKET CONN. KITS,PV4-PF2.5

Also in the Series | SOLARLOK PV4-PM Connector



Solar Connectors & Adapters(5)


Customers Also Bought



TE Part #2273012-4
M8 x 1.0 Angled socket Pigtail LED



TE Part #1-1423673-8
W51-A151A1-15=CKTBKR,THERM, ROC



TE Part #1-796949-8
18POS TERMI-BLOK PCB MOUNT



TE Part #1-1579004-2
CSV10 CRIMPING HANDTOOL SOLARLOK 4-6



TE Part #8-1419125-5
SDT-S-106LMR,000



TE Part #2106831-1
Grounding Assy



TE Part #1-1393250-7
W28-XQAT-15=W28

Documents

Product Drawings

SOCKET CONN. KITS,PV4-PF2.5

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-1971920-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1971920-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1971920-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOLARLOK PV4-PM CONNECTOR 1000V DC](#)

English

[SOLARLOK PV4-S DC CRIMP CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[TUV Certificate](#)

English

[TUV Certificate](#)

English