


**06800035**

RCK 80 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**
**Technical Specifications**

Part number (CODE)	06800035
Ød (DD) mm	35
ØD (D) mm	47
D1 (D1) mm	62
D2 (D2) mm	69
L1 (L1) mm	31
L2 (L2) mm	45.5
L3 (L3) mm	52.5
L (L) mm	58.5
Maximum torque Mt (MT) Nm	790
Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>	105
Clamping pressure - Hub (CPH) N/mm <sup>2</sup>	80
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x18
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	17.0