




- 1. MATERIAL:
BODY & CENTER CONTACT - COPPER ALLOYS.
INSULATOR - TEFLON (PTFE).
- 2. FINISH:
BODY, INSERT & CENTER CONTACT - GOLD PLATE, PER ASTM B488
OVER NICKEL PLATE PER, SAE-AMS-QQ-N-290
- 3. CONTACTS TO BE TERMINATED TO RG405 OR SIMILAR CABLES.

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED PER ECN-25-306091	14FEB2025	LS	FB

PERFORMANCE CHARACTERISTIC	REQUIREMENT
CONTACT	RF SIZE 12 COAX
CONNECTOR	38999 SERIES III
FREQUENCY	DC-65 GHz
IMPEDANCE	50 OHMS
TEMPERATURE	-65°C - +165°C
DURABILITY	500 CYCLES



CABLE PREPARATION FOR Ø.086 FLEX, SEMI-RIGID OR CONFORMABLE CABLES



2389333-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN HARISH D 19MAY2021			PIN CONTACT ASSY, RF SIZE 12 COAX	
DIMENSIONS: INCHES		CHK SUDHAKAR NS 19MAY2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD EUGENE G 19MAY2021				
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.001 [0.03] 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-160810				
MATERIAL SEE NOTES		FINISH SEE NOTES	APPLICATION SPEC 408-160087	NAME	RESTRICTED TO	
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2389333	
CUSTOMER DRAWING			SCALE 15:1	SHEET 1 OF 1	REV A	