

2301841-1 ✓ ACTIVE

AMPLIMITE

TE Internal #: 2301841-1

25 Position D-Shaped Connector, Receptacle, Wire-to-Board,
Board Mount, Shell Size 3, 2.77 mm [.109 in] Centerline, Printed
Circuit Board, Signal

[View on TE.com >](#)



Connectors > D-Shaped Connectors



Number of Positions: **25**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Connector Mounting Type: **Board Mount**

Connector Shell Size: **3**

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Connector Shell Size	3
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	25
Number of Rows	2
PCB Mount Orientation	Vertical

Body Features

Primary Product Color	Black
Connector Profile	High

Contact Features

Contact Shape & Form	Round
Contact Current Rating (Max)	1.5 A



Contact Options	Installed
-----------------	-----------

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Diameter	.6 mm[.023 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention	With
Mating Retention Type	Threaded Inserts, 4-40 UNC

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2.77 mm[.109 in]

Dimensions

Row-to-Row Spacing	2.84 mm[.111 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2301835-2
 AMPL PLUG HD20, VERT, 25P, B/L,4-40 S/LO

Customers Also Bought




TE Part #3-1625892-7
 3W SM M/OX 5% 2K2



TE Part #1625958-2
 HB01RE 100K 1% 100PPM



TE Part #1879011-5
 SMF2 330R 5%



TE Part #8-1879255-5
 RP 2B 100R 0.1% 15PPM CUT LENG



TE Part #7-1879260-9
 RP 2B 4K99 0.1% 15PPM CUT LENG



TE Part #7-1879261-0
 RP 2B 10K2 0.1% 15PPM CUT LENGTH



TE Part #5-2176400-8
 3540 240R 1%



TE Part #2301826-1
 AMPL PLUG HD20, VERT, 9P, B/L,4-40 INS



Documents

Product Drawings

[AMPL REC HD20, VERT, 25P, B/L,4-40 INS](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2301841-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2301841-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2301841-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English