

M18 FLAG230XPDB-121C

M18 FUEL™ 230 MM LARGE BRAKING GRINDER WITH PADDLE SWITCH

- The world's first single 18V battery operated large angle grinder that delivers the power to grind, lighter than corded tools and makes up to 68 cuts per charge in 42 mm stainless steel pipe
- The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries
- Disc brake slows the disc down faster for improved user protection
- Non-lockable safety paddle switch with line-lock-out function to prevent automatic start up
- Keyless guard for great cutting capacity and fast guard adjustment without using a key
- FIXTEC™ nut for tool-free disc change
- Anti-vibration side handle for lower vibration
- Removable dust screen to prevent debris entrance, prolonging motor life
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

No load speed (rpm)	6600
Brake	Yes
Anti-kickback protection	Yes
Switch type	Paddle (Deadman) switch
FIXTEC™	Yes
Kit included	1 x M18 FB12 Battery pack, M12-18 FC Charger, Kitbox
Article Number	4933499241

