

Main

Range of product	Actassi
Product or component type	19" fibre optic panel
Provided equipment	1 transparent cover rear 2 quick fix 19" mounting 2 coiling wheel 2 transparent cover front 2 Pg 9 cable gland 3 blanking plate 4 label holder 2 pop rivet
Colour	Dark grey (RAL 7016)

Complementary

Product compatibility	3 adaptor plate
Device composition	Without connectors
Number of connectors	24
Number of optic fibre	48
Number of rack unit	1U
Material	DC01 1.2 mm metal sheet PA6 plastic part PA66 GF20 plastic part PC plastic part PMMA (polymethyl methacrylate) plastic part
Height	45 mm
Width	490 mm
Depth	300 mm
Net weight	4.7 kg
Targeted region	Europe Asia Pacific.

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 NF C 20-150

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations