



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2G
Product or component type	Switch-disconnector-fuse
Poles description	4P
Protected poles description	4t
Contacts type and composition	4 NO
[I _{th}] conventional free air thermal current	63 A (at 40 °C)
[I _e] rated operational current	40 A at 440 V 2 poles in series per phase DC-23A 40 A at 440 V 2 poles in series per phase DC-23B 63 A at 400 V AC-23A 63 A at 400 V AC-23B 63 A at 500 V AC-23A 63 A at 500 V AC-23B 63 A at 690 V AC-23A 63 A at 690 V AC-23B
Fuse type	DIN
Fuse size	000
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External left side
Mounting support	Plate
[U _i] rated insulation voltage	750 V AC 50/60 Hz
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	30 kW at 400 V 40 kW at 500 V 55 kW at 690 V
Making capacity	630 A at 400 V AC-23B
Breaking capacity	500 A at 400 V (AC-23B)
Short-circuit withstand	10.6 kA
Mechanical durability	10000 cycles
Electrical durability	1500 Cycles AC-23A 1500 Cycles DC-23A 300 Cycles AC-23B 300 cycles DC-23B
Connections - terminals	Power circuit: lugs-ring terminals 10...25 mm ²
[I _{cm}] rated short-circuit making capacity	100 kA at 400 V with protection by gG fuses
Tightening torque	Power circuit: 3.2 N.m

Environment

Standards	IEC 60947-3
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	118 mm
Width	168 mm
Depth	116.5 mm
Net weight	1.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information