

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600

<https://www.phoenixcontact.com/in/products/1162600>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP VARIOFACE front adapter, with connected system cables for ControlLogix® 1756 I/O. Up to 2 x 8 channels can be connected.

Your advantages

- Individual I/O modules lock to the controller for connection security
- Disconnect lever aids in removal from I/O card
- Marking label can be attached
- Pluggable screw terminals on adapter for power connection

Commercial data

Item number	1162600
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK232R
GTIN	4063151173173
Weight per piece (excluding packing)	940 g
Country of origin	DE

1162600

<https://www.phoenixcontact.com/in/products/1162600>

Technical data

Product properties

Product type	Front adapter
Product family	VARIOFACE Professional

Electrical properties

Max. permissible operating voltage	120 V AC
Max. permissible current	1 A (per path)
	3 A (per group, positive terminals)
	8 A (per group, negative terminals)

Supported controller ALLEN-BRADLEY ControlLogix

Suitable I/O card	1756-IA16
	1756-IB16
	1756-IC16
	1756-IN16

Connection data

Controller level

Connection method	Plug-in connection
Note	Can be plugged onto 20-pos. I/O modules

Field level

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	2
Number of positions	14
Pitch	2.54 mm

Supply

Connection method	Push-in / plug connection
Stripping length	9 mm
Conductor cross section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	26 ... 16

Dimensions

Item dimensions

Width	344.822 mm
Height	47.352 mm
Depth	56.345 mm

Cable

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600

<https://www.phoenixcontact.com/in/products/1162600>

Length	6 m
--------	-----

Cable/line

14X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	14
Shielded	no
Cable type	14X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	14x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	6.40 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	55 mm
Smallest bending radius, movable installation	104 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Front adapter with splitting cable for two modules

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	0 °C ... 80 °C
Altitude	≤ 2000 m (Above sea level)
Permissible humidity (operation)	≤ 95 % (non-condensing)

Standards and regulations

Standards/regulations	UL 61010-2-201
-----------------------	----------------

Notes

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600


<https://www.phoenixcontact.com/in/products/1162600>

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Drawings

Circuit diagram



1162600

<https://www.phoenixcontact.com/in/products/1162600>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1162600>

	UL classified Approval ID: E238705
	cUL Classified Approval ID: E238705
	cUL Recognized Approval ID: E196811
	UL Recognized Approval ID: E196811
cULus Classified	
cULus Recognized	

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600

<https://www.phoenixcontact.com/in/products/1162600>

Classifications

ECLASS

ECLASS-11.0	27242292
ECLASS-12.0	27242292
ECLASS-13.0	27242292

ETIM

ETIM 9.0	EC002584
----------	----------

1162600

<https://www.phoenixcontact.com/in/products/1162600>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	24fc5f8d-47e9-4d4e-954a-086010c6896d

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600

<https://www.phoenixcontact.com/in/products/1162600>

Accessories

VIP-2/SC/FLK14/PLC - Passive module

2315214

<https://www.phoenixcontact.com/in/products/2315214>

VARIOFACE interface module for 8 channels



VIP-2/PT/FLK14/PLC - Passive module

2903801

<https://www.phoenixcontact.com/in/products/2903801>

VARIOFACE interface module, with push-in connection for 8 channels



VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter

1162600

<https://www.phoenixcontact.com/in/products/1162600>



VIP-2/SC/FLK14/LED/PLC - Passive module

2322249

<https://www.phoenixcontact.com/in/products/2322249>

VARIOFACE interface module, with LED, for 8 channels



VIP-2/PT/FLK14/LED/PLC - Passive module

2904279

<https://www.phoenixcontact.com/in/products/2904279>

VARIOFACE interface module, with push-in connection and light indicator, for 8 channels



VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter

1162600

<https://www.phoenixcontact.com/in/products/1162600>



VIP-2/SC/FLK14/8P/PLC - Termination board

2322294

<https://www.phoenixcontact.com/in/products/2322294>



VARIOFACE interface module, for 8 channels, each with an additional terminal block per signal for a common plus potential

VIP-2/PT/FLK14/8P/PLC - Termination board

2904284

<https://www.phoenixcontact.com/in/products/2904284>



VARIOFACE interface module, for 8 channels, each with an additional terminal block per signal for a common plus potential

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter




1162600

<https://www.phoenixcontact.com/in/products/1162600>

FLKM 14/KDS3-MT/PPA/PLC - Passive module

2290423

<https://www.phoenixcontact.com/in/products/2290423>



VARIOFACE interface module, for 8 channels with knife disconnect terminal blocks and test sockets to the peripherals and the system

PLC-V8/FLK14/IN - System connection

2296553

<https://www.phoenixcontact.com/in/products/2296553>



V8 adapter for 8 x PLC-INTERFACE (6.2 mm), controller: PLC system cabling of input cards, connection 1: IDC/FLK pin strip 1x 14-position, connection 2: Plug-in connection (Can be snapped onto 8x PLC-INTERFACE terminals), connection 3: Screw connection 1x 2-position, number of channels: 8, control logic: positive switching

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter

1162600

<https://www.phoenixcontact.com/in/products/1162600>



KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/in/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, text field height: 8 mm, text field width: 20 mm

SF-SL 1,0X5,5-150 - Screwdriver

1212552

<https://www.phoenixcontact.com/in/products/1212552>



Screwdriver, bladed (lasered), size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

VIP-PA-2X14/26/ 6,0M/1756/062 - Front adapter



1162600

<https://www.phoenixcontact.com/in/products/1162600>

ZBF10:UNBEDRUCKT - Zack Marker strip, flat

0809997

<https://www.phoenixcontact.com/in/products/0809997>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 10 mm, Number of individual labels: 10, text field height: 10 mm, text field width: 5.15 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in