



26M024D

Electrical Data	26M024D1U Unipolar	26M024D2U Unipolar	26M024D1B Bipolar	26M024D2B Bipolar	
1 Operating Voltage	5	12	5	12	VDC
2 Resistance per Phase, ± 10%	19.6	110.0	19.8	108.0	Ohms
3 Inductance per Phase, typ	3.8	26.6	9.0	44.3	mH
4 Rated Current per Phase *	0.26	0.11	0.25	0.11	A
Coil independent parameters					
5 Holding Torque, MIN *	9.5 (1.35)	9.5 (1.35)	12 (1.7)	12 (1.7)	mNm (oz-in)
6 Detent Torque, Max	4.2 (0.6)	4.2 (0.6)	4.2 (0.6)	4.2 (0.6)	mNm (oz-in)
7 Rotor inertia	1.1 (0.00601)	1.1 (0.00601)	1.1 (0.00601)	1.1 (0.00601)	(gcm ²) (oz-in-s ²)
8 Step Angle	15.0	15.0	15.0	15.0	Degree
9 Absolute accuracy 2 ph. On, Full step	± 1	± 1	± 1	± 1	Degree
10 Steps per Revolution	24	24	24	24	
11 Ambient Temp Range (operating)	-20 to +70 (-4 to +158)	-20 to +70 (-4 to +158)	-20 to +70 (-4 to +158)	-20 to +70 (-4 to +158)	°C (°F)
12 Maximum Coil Temperature	130 (266)	130 (266)	130 (266)	130 (266)	°C (°F)
13 Bearing Type	Sintered Bronze Sleeve	Sintered Bronze Sleeve	Sintered Bronze Sleeve	Sintered Bronze Sleeve	
14 Insulation Resistance at 500 VDC	100	100	100	100	Mohms
15 Dielectric Withstanding Voltage	650 for 2 seconds	650 for 2 seconds	650 for 2 seconds	650 for 2 seconds	VAC
16 Weight	34 (1.2)	34 (1.2)	34 (1.2)	34 (1.2)	g (oz)
17 Leadwire	AWG 28, UL 1429	AWG 28, UL 1429	AWG 28, UL 1429	AWG 28, UL 1429	

All Motor Data Values at 20°C Unless Otherwise Specified

* Energize at Rated Current, 2 Phase On

