

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sensor/actuator cable, 5-position, PVC, yellow, free cable end, on Socket straight M12, coding: A, cable length: 5 m



Commercial data

Item number	1409636
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AF1IGC
Product key	AF1IGC
GTIN	4055626018690
Weight per piece (including packing)	249 g
Weight per piece (excluding packing)	249 g
Customs tariff number	85444290
Country of origin	US

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Technical data

Notes

General	These cable assemblies are UL/cUL listed for use in Class I, Division 2 (CID2) hazardous locations.
---------	---

Product properties

Product type	Sensor/actuator cable
Application	U.S. cables for hazardous locations
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PVC

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	No

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

Connection 1

Type	free cable end
------	----------------

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	43 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	5
Shielded	no
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Wire diameter incl. insulation	1.27 mm ±0.03 mm
External cable diameter	5.40 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material, filler	PP
Material wire insulation	PVC
Single wire, color	brown, blue, black, white, gray
Overall twist	5 wires around filler to the core
Max. conductor resistance	max. 50.5 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, movable installation	44 mm
Flame resistance	FT4
Other resistance	UV resistant
Special properties	UL standards PLTC and ITC
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

Approvals

Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D
------------------	------------------------------------

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable

1409636

<https://www.phoenixcontact.com/gb/products/1409636>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable


1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Dimensional drawing




EXCLIP socket



EXCLIP mounted plug

Dimensional drawing




SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable

1409636


<https://www.phoenixcontact.com/gb/products/1409636>

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1409636>



cUL Listed

Approval ID: FILE E 359524

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	150 V	4 A	-	-



UL Listed

Approval ID: FILE E 359524

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	150 V	4 A	-	-

cULus Listed

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-HZ-5P- 5,0-542/M12FS BK - Sensor/actuator cable



1409636

<https://www.phoenixcontact.com/gb/products/1409636>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk