


Features

- 5G/LTE
- 2x2 MIMO
- 617-6000 MHz
- 7 dBi
- Wi-Fi 6E
- Directional
- IP68
- -40°C to 80°C

RS PRO Multi-Band Antennas

Antenna Directional for RS PRO 2768463

RS Stock No.: 0434530



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

INTEGRATED MULTI-BAND LTE DIRECTIONAL ANTENNA + WI-FI 6E ANTENNA + POE SPLITTER + PLACE TO INSTALL 2768464 (ALL-IN-ONE)

Directional all-in-one antenna for 2768464 router is a perfect outdoor device for improving the signal in rural/suburban and locations where the mobile signal is weak. It has embedded directional LTE and Wi-Fi 6E antenna. If you use 2768464 with this all-in-one antenna, you get an integrated complete solution with embedded router and multi band antennas in one enclosure.

The set contains a Passive PoE splitter, allowing you to split data and power from a single Ethernet cable and maintain gigabit transfer speeds while protecting the LAN port from damage caused by overvoltage, short circuit or improper connection.

Wi-Fi 6E support!

5G / LTE SPECIFICATION

FREQUENCY	617 - 960 MHz 1.7 - 2.7 GHz 3.3 - 4.6 GHz 4.7 - 6.0 GHz
GAIN	617 - 960 MHz : 6 dBi 1.7 - 2.7 GHz : 7 dBi 3.3 - 4.6 GHz : 7 dBi 4.7 - 6.0 GHz : 5.5dBi
SUPPORTED LTE BANDS	1, 2, 3, 4, 5, 7, 8, 9, 10, 12, 13, 14, 17, 18, 19, 20, 22, 25, 26, 27, 28, 29, 30, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 46, 47, 48, 49, 52, 53, 65, 66, 67, 68, 69, 71, 85, 103, 106
SUPPORTED 5G BANDS	n1, n2, n3, n5, n7, n8, n12, n13, n14, n18, n20, n25, n26, n28, n29, n30, n34, n38, n39, n40, n41, n46, n47, n48, n53, n65, n66, n67, n71, n77, n78, n79, n80, n81, n82, n83, n84, n85, n86, n89, n90, n95, n97, n98, n100, n101, n256
VSWR	<2.00, max <3.00
BEAMWIDTH	80°/80° ±15°
POLARIZATION	X (+-45degrees)
IMPEDANCE	50 Ω

WI-FI SPECIFICATION

FREQUENCY	2.4 - 2.5 GHz 5.0 - 7.2 GHz
GAIN	2.4 - 2.5 GHz: 6dBi 5 GHz: 7.5dBi 7 GHz: 7.5dBi
VSWR	< 1.50, max < 2.00
BEAMWIDTH	360°/25°
POLARIZATION	Vertical
IMPEDANCE	50 Ω

MECHANICAL SPECIFICATION

MATERIALS	ABS, aluminum, PTFE, Fiberglass
CONNECTOR TYPE	RJ45
INGRESS PROTECTION	IP68
DIMENSIONS	269 x 269.5 x 177 mm 10.6 x 10.6 x 7 inch
WEIGHT	2.8 kg 6.17 lbs
OPERATING TEMPERATURE	From -40°C to 80°C From -40°F to 176°F


MOUNTING KIT SPECIFICATION

DIMENSIONS	9.9 x 10.5 x 14.8 cm 3.9 x 4.13 x 5.83 inch
REGULATION RANGE	+/- 30°
MAST DIAMETER RANGE	25 - 60mm 0.98-2.36 inch
MATERIAL	Polyamide with fiberglass + galvanized steel U-Bolts
WEIGHT	0.87kg
MOUNTING PLACE	Wall or mast or ceiling


DEVICE SPECIFICATION

SPECIFICATION	<p>Category: Passive Components Subcategory: Antennas Type: Multi-Band Antennas, WiFi Antennas, Brand: RS PRO Frequency Range: 617 – 6000 MHz RF Protocols: 5G, LTE, WiFi6 E Gain: 7 dBi Internal/External : External Antena Directivity: Directional Antenna Mounting type: Ceiling, Wall/Pole Mounting Type: Bracket Mount, Pole Mount, Pole Mount, Wall Mount Antena Physical Form: Panel, Square,</p>
----------------------	---


5G/LTE PLOTS




PORT 1 - 5G/LTE from 650MHz to 950MHz




PORT 1 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 1 - 5G/LTE from 2.3GHz to 2.7GHz




PORT 1 - 5G/LTE from 3.3GHz to 3.8GHz




PORT 1 - 5G/LTE from 4.2GHz to 4.6GHz




PORT 1 - 5G/LTE from 5.0GHz to 5.9GHz




PORT 2 - 5G/LTE from 650MHz to 950MHz




PORT 2 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 2 - 5G/LTE from 2.3GHz to 2.7GHz




PORT 2 - 5G/LTE from 3.3GHz to 3.8GHz





PORT 2 - 5G/LTE from 4.2GHz to 4.6GHz



PORT 2 - 5G/LTE from 5.0GHz to 5.9GHz



WI-FI PLOTS



Wi-Fi 2.4GHz and 5GHz and 6GHz

