

ENGLISH

Datasheet

RS Pro RS Series Thick Film Surface Mount Resistor 0805 Case $33\Omega \pm 5\% \ 0.125W \pm 200 ppm/^{\circ}C$

RS Stock No: 713-6816



Product Details

RS Pro 0805 thick film surface mount resistor with $\pm 5\%$ tolerance, provides 33 Ω resistance and is power rated at 0.125 W. The temperature coefficient of resistance is ± 200 ppm/°C. Applications include telecommunication equipment, radio and tape recorders, TV tuners, video cameras, watches, pocket calculators, automotive industry, computers, instruments, medical and military equipment.

Features and Benefits

- Small size and lightweight
- Highly reliable multilayer electrode construction
- Compatible with all soldering process





Specifications:

opecifications.	
Case Style	Ruthenium Oxide
Depth	1.25 mm
Dimensions	2 x 1.25 x 0.5 mm
Height	0.5 mm
Length	2 mm
Maximum Operating Temperature	+155°C
Maximum Temperature Coefficient	+200 ppm/°C
Minimum Operating Temperature	-55°C
Minimum Temperature Coefficient	-200 ppm/°C
Package/Case	0805
Power Rating	0.125 W
Resistance	33 Ω
Technology	Thick Film
Temperature Coefficient	±200 ppm/°C
Termination Style	Solder Pad
Tolerance	±5%
Maximum Operating Voltage	150 V
Maximum Overload Voltage	300 V
Tape Width	8 mm




ENGLISH

Thick Film Chip Resistor 5% - RS Series

0201/0402/0603/0805/1206

■Construction




1	Alumina Substrate	4	Edge Electrode (NiCr)	7	Resistor Layer (RuO ₂ /Ag)
2	Bottom Electrode (Ag)	(3)	Barrier Layer (Ni)	8	Primary Overcoat (Glass)
3	Top Electrode (Ag-Pd)	6	External Electrode (Sn)	9	Secondary Overcoat (Epoxy)


■Dimensions

Unit: mm


Туре	Size (Inch)	L	w	т	D1	D2	Weight (g) (1000pcs)
RS-0201	0201	0.60±0.03	0.30±0.03	0.23±0.03	0.15±0.05	0.15±0.05	0.150
RS-0402	0402	1.00±0.05	0.50±0.05	0.35±0.05	0.20±0.10	0.20±0.10	0.620
RS-0603	0603	1.60±0.10	0.80±0.10	0.45±0.10	0.30±0.20	0.30±0.20	2.042
RS-0805	0805	2.00±0.10	1.25±0.10	0.50±0.10	0.35±0.20	0.40±0.20	4.368
RS-1206	1206	3.10±0.10	1.55±0.10	0.55±0.10	0.50±0.25	0.50±0.20	8.947

■Part Numbering












■Derating Curve


ENGLISH




■Standard Electrical Specifications

Item	Power Rating at 70°C Jumper	Operating Temp. Range	Max. Operating	Max. Overload	Resistance Range	TCR (PPM/°C)
Туре	Rated Current	19	Voltage	Voltage	±5%	(5)
RS-0201	1/20W	55 ~ +155°C	25V	50V	1Ω – 9.76ΜΩ	±200
Jumper	1A	-55 ~ +155 ·C	250	50 V	0Ω (< 50 m Ω)	-
RS-0402	1/16W	55 .45500 501/		100V	1Ω – 9.76ΜΩ	±200
Jumper	1A	55 ∼ +155°C	50V	1000	0Ω (<50m Ω)	-
RS-0603	1/10W	55 145500	75V	150V	1Ω – 9.76ΜΩ	±200
Jumper	1A	55 ∼ +155°C	750	1500	0Ω (< 50 m Ω)	-
RS-0805	1/8W	FF	4		1Ω – 9.76ΜΩ	±200
Jumper	2A	55 ∼ +155°C	150V	300V	0Ω (< 50 m Ω)	-
RS-1206	1/4W	FF 14FF00	2001/	4001/	1Ω – 9.76ΜΩ	±200
Jumper	2A	55 ∼ +155°C	200V	400V	0Ω (<50mΩ)	-

■Soldering Condition





IR Reflow Soldering

Wave Soldering (Flow Soldering)

- (1) Time of IR reflow soldering at maximum temperature point 260°C: 10s
- (2) Time of wave soldering at maximum temperature point 260°C: 10s
- (3) Time of soldering iron at maximum temperature point 410°C: 5s



ENGLISH

■Environmental Characteristics

Itom	Requ	irement	Test Method		
Item	±5% Jumper		Test Method		
Temperature Coefficient of	As Spec.		JIS-C-5201-1 4.8 IEC-60115-1 4.8		
Resistance (T.C.R.)			-55°C~+125/+155°C, 25°C is the reference temperature		
0	. (0.00(0.000)	.50	JIS-C-5201-1 4.13 IEC-60115-1 4.13		
Short Time Overload	±(2.0%+0.05Ω)	<50mΩ	RCWV*2.5 or Max. overload voltage for 5 seconds, 2 seconds for high power series		
Insulation Resistance	≥10G		JIS-C-5201-1 4.6 IEC-60115-1 4.6		
			Max. overload voltage for 1 minute		
Endonesia	. (0.00(+ 0.400)	*100m*O	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1		
Endurance	±(3.0%+0.10Ω)	<100mΩ	70±2°C, Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"		
		<100mΩ	JIS-C-5201-1 4.24		
Damp Heat with Load	±(3.0%+0.10Ω)		$40\pm2^{\circ}$ C, 90~95% R.H. Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"		
Dry Heat	±(1.5%+0.10Ω)	<50mΩ	JIS-C-5201-1 4.23 IEC-60115-1 2.23.2		
			at +125/+155°C for 1000 hrs		
			JIS-C-5201-1 4.33 IEC-60115-1 4.33		
Bending Strength	$\pm (1.0\% + 0.05\Omega)$	<50mΩ	Bending once for 5 seconds		
			2010, 2512 sizes: 2mm Other sizes: 3mm		
Solderability	95% min. coverage		JIS-C-5201-1 4.17 IEC-60115-1 4.17		
,	3		245±5°C for 3 seconds		
Resistance to Soldering Heat	±(1.0%+0.05Ω)	<50mΩ	JIS-C-5201-1 4.18 IEC-60115-1 4.18		
3	_(,		260±5°C for 10 seconds		
Voltage Proof	No breakdown or flashover		JIS-C-5201-1 4.7 IEC-60115-1 4.7		
			1.42 times RCWV (RMS) for 1 minute		
Leaching	Individual leaching		JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1		
J	Total leaching are	a 10%	260±5°C for 30 seconds		
Rapid Change of Temperature	emperature $\pm (1.0\% + 0.05\Omega)$		JIS-C-5201-1 4.18 IEC-60115-1 4.18		
. •	,		-55°C to +125/+155°C, 5 cycles		


■ Storage Temperature: 25±3°C; Humidity < 80%RH



Packaging

Reel Specifications & Packaging Quantity






Unit: mm

Туре	Packaging Quantity	Tape Width	Reel Diameter	ФА	ФВ	ФС	W	Т
RS-0201 RS-0402			7 inch	178.5±1.5	60+1/-0	13.0±0.2	9.0±0.5	12.5±0.5
RS-0603	Paper	per 8mm	10 inch	254±1	100±0.5	13.0±0.2	9.5±0.5	13.5±0.5
RS-0805 RS-1206	0805		13 inch	330±1	100±0.5	13.0±0.2	9.5±0.5	13.5±0.5

Paper Tape Specifications



Unit: mm

Туре	Α	В	W	E	F	P ₀	P ₁	P ₂	ΦD_0	Т
RS-0201	0.38±0.05	0.68±0.05	8.0±0.2	1.75±0.1	3.50±0.05	4.00±0.10	2.00±0.05	2.00±0.05	1.50+0.1,-0	0.42±0.1
RS-0402	0.65±0.10	1.15±0.1	8.0±0.2	1.75±0.1	3.50±0.05	4.00±0.10	2.00±0.05	2.00±0.05	1.50+0.1,-0	0.45±0.1
RS-0603	1.10±0.10	1.90±0.1	8.0±0.2	1.75±0.1	3.50±0.05	4.00±0.10	4.00±0.05	2.00±0.05	1.50+0.1,-0	0.70±0.1
RS-0805	1.60±0.10	2.40±0.2	8.0±0.2	1.75±0.1	3.50±0.05	4.00±0.10	4.00±0.05	2.00±0.05	1.50+0.1,-0	0.85±0.1
RS-1206	1.90±0.10	3.50±0.2	8.0±0.2	1.75±0.1	3.50±0.05	4.00±0.10	4.00±0.05	2.00±0.05	1.50+0.1,-0	0.85±0.1



■Marking

ENGLISH

Unit: mm


No Marking for 0201 and 0402

Jumper for all: Letter "0"

5% for 0603/0805/1206: 3 digits marking in E24

Example: $101=100\Omega$ $102=1K\Omega$ (1 and 2 are E24 code and 3 code is multiplier)

■Recommend Land Pattern



_	_	_	
Type	Α	В	С
RS-0201	0.30	0.25	0.30
RS-0402	0.50	0.45	0.60
RS-0603	0.90	0.60	0.90
RS-0805	1.20	0.70	1.30
RS-1206	2.00	0.90	1.60

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.