

# CA-06P1N8AT0DNS - Cable connector



1619447  
<https://www.phoenixcontact.com/gb/products/1619447>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243565



## Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

Item number	1619447
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	ABRAED
Product key	ABRAED
Catalog page	Page 90 (C-2-2019)
GTIN	4046356824002
Weight per piece (including packing)	194.7 g
Weight per piece (excluding packing)	194.7 g
Customs tariff number	85366990
Country of origin	DE

# CA-06P1N8AT0DNS - Cable connector



1619447

<https://www.phoenixcontact.com/gb/products/1619447>

## Technical data

### Notes

Order information:	Order crimp contacts 6 x Ø 2 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Data management status

Article revision	06
------------------	----

### Connector

#### Insulating body

Note	Order information: Order crimp contacts 6 x Ø 2 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Contact diameter	Signal contacts 2 mm
Litz wire cross-section	Signal contacts min. 1 mm <sup>2</sup>
Litz wire cross-section	Signal contacts max. 2.5 mm <sup>2</sup>
Nominal current per signal contact	20 A
Rated voltage	Signal contact 48 V AC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Housing material	Metal
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

#### Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

## Environmental and real-life conditions

# CA-06P1N8AT0DNS - Cable connector



1619447

<https://www.phoenixcontact.com/gb/products/1619447>

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

# CA-06P1N8AT0DNS - Cable connector




1619447

<https://www.phoenixcontact.com/gb/products/1619447>

## Drawings

Schematic diagram



Connector pin assignment

# CA-06P1N8AT0DNS - Cable connector





1619447

<https://www.phoenixcontact.com/gb/products/1619447>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1619447>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	10 A	14 - 14	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	17 A	14 - 14	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# CA-06P1N8AT0DNS - Cable connector



1619447

<https://www.phoenixcontact.com/gb/products/1619447>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-06P1N8AT0DNS - Cable connector



1619447  
<https://www.phoenixcontact.com/gb/products/1619447>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a1a03172-e107-4158-857a-fbc5fc9e1257

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)