



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold (Au)**
Contact Size: **Size 20**
Contact Base Material: **Copper Alloy**
Product Terminates To: **Printed Circuit Board**

Features

Contact Features

Contact Underplating Material	Copper
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Contact Size	Size 20
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	5 A

Termination Features

Termination Post & Tail Diameter	.02 mm[.51 in]
Termination Post & Tail Length	.33 mm[8.38 in]
Product Terminates To	Printed Circuit Board

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.6% in 74018820) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #0063733001
55A1122-28-0/2-9



TE Part #207683-8
AMPLIMITE,PIN CONT,SZ 22D



TE Part #CV7361-000
202K132-25L-0



TE Part #NB15734001
RNF-150-1/8-0-SP



TE Part #1-34070-1
PG BUTT SPLC 22-16COMM22-18MIL



TE Part #207684-4
AMPLIMITE,SKT CONT,SZ 22



TE Part #206803-2
AMPLIMITE RECEPT ASY,37 POS,



TE Part #SP44907X-30
44907X GSFC 311P18-07A101



TE Part #CAT-HST-RNF100-3
RNF-100-3 Heat Shrink Tubing

Documents

Product Drawings
AMPLIMITE,PIN CONT,SZ 20,AU PLTD
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-212565-0_Z.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-212565-0_Z.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-212565-0_Z.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English