



Figure similar

NEOZED, fuse base, D03, 1-pole, 100 A, Un AC: 400 V, Un DC: 250 V, without cover incoming terminal: screw head contact outgoing terminal: saddle terminal snap-on mounting (DIN rail)

Model		
product brand name	NEOZED	
product designation	Fuse base	
design of the product	NEOZED fuse base installation	
product version	Without cover	
General technical data		
number of poles	1	
size of fuse system according to EN 60269-1	D03	
Supply voltage		
operating voltage rated value	400 V	
Dissipation		
power loss [W] for rated value of the current at AC in hot operating state per pole	2.5 W	
Main circuit		
operational current rated value	100 A	
Product details		
product component cover	No	
Mechanical Design		
height	86 mm	
width	44.9 mm	
depth	44 mm	
fastening method	DIN rail	
net weight	204 g	
material of D fuse base	porcelain	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG1812>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/5SG1812>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1812

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/12/2025 

