


## MIRO TR 24VDC FK 5P OPTO-COUPLER MODULE


IN: 48 VDC - OUT: 35 VDC / 2 A

Transistor 2 A  
 24 V DC  
 short-circuit protected  
 Switching frequency: max. 1 kHz  
 Spring clamp terminals

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Input

Voltage range ON	10...48 V DC
Voltage range OFF	0...5 V DC
Control current	6 mA
LED display	LED (yellow)

### General data

Test isolation voltage	3.75 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

### Output

Switching voltage	10...35 V DC
Switching current per output	1 mA...2 A (short-circuit protected)
Saturation voltage (across output)	max. 1.2 V DC
Leakage current (output is open)	max. 0.1 mA
Switching time ON/OFF	90/120 μs
Switching frequency	max. 1 kHz

### Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1