

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : ULTRACUT EVO 255
UFI : 4910-G01E-K00S-AGR5

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : Industrial
For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315
Serious eye damage/eye irritation, Category 1 H318
Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS05

Signal word (CLP) :

Danger

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains	: ALKOXYAMINE
Hazard statements (CLP)	: H315 - Causes skin irritation. H318 - Causes serious eye damage. H412 - Harmful to aquatic life with long lasting effects.
Precautionary statements (CLP)	: P264 - Wash hands thoroughly after handling. P280 - Wear protective clothing, eye protection, face protection, protective gloves. P302+P352 - IF ON SKIN: Wash with plenty of soap and water. P305+P351+P338+P310 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALKOXYAMINE	(CAS-No.) 111-42-2 (EC-No.) 203-868-0 (REACH-no) 01-2119488930-28	5 – 10	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 STOT RE 2, H373
ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED	(CAS-No.) 68920-66-1 (EC-No.) 500-236-9 (REACH-no) 01-2119489407-26	5 – 10	Skin Irrit. 2, H315 Aquatic Acute 1, H400 Aquatic Chronic 3, H412
ALKENYL ALKANOL AMIDE	(CAS-No.) 68603-38-3 (EC-No.) 271-653-9 (REACH-no) 01-2119951823-33	2.4 – 5	Skin Irrit. 2, H315 Eye Irrit. 2, H319 Aquatic Chronic 2, H411
SODIUM PYRITHIONE	(CAS-No.) 3811-73-2 (EC-No.) 223-296-5	0.1 – 1	Acute Tox. 4 (Oral), H302 Acute Tox. 3 (Dermal), H311 Acute Tox. 4 (Inhalation), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Aquatic Acute 1, H400 (M=100) Aquatic Chronic 1, H410 (M=10)

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention. Specific treatment (see supplemental first aid instruction on this label). Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact : Causes skin irritation.
Symptoms/effects after eye contact : Causes serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters. Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.
Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.
Hygiene measures : Wash hands, forearms and face thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:

Chemical goggles or safety glasses

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Wear protective gloves.

8.2.2.3. Respiratory protection

Respiratory protection:

Wear appropriate mask

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Gold.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available.
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available.
Freezing point	: No data available
Boiling point	: 100 °C
Flash point	: > 100 °C
Auto-ignition temperature	: > 200
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available.
Relative density	: 0,95
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)

LD50 oral rat	> 2000 mg/kg
---------------	--------------

ALKENYL ALKANOL AMIDE (68603-38-3)

LD50 oral rat	> 3000 mg/kg
---------------	--------------

LD50 dermal	> 2000 mg/kg
-------------	--------------

Skin corrosion/irritation : Causes skin irritation.
pH: No data available.

Serious eye damage/irritation : Causes serious eye damage.
pH: No data available.

Respiratory or skin sensitisation : Not classified

Additional information : Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

ALKOXYAMINE (111-42-2)

NOAEL (chronic, oral, animal/male, 2 years)	64 mg/kg bodyweight Animal: rat, Animal sex: male, Guideline: OECD Guideline 451 (Carcinogenicity Studies), Remarks on results: other:Effect type: carcinogenicity (migrated information)
---	---

Reproductive toxicity : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

STOT-repeated exposure : Not classified

Additional information : Based on available data, the classification criteria are not met

ALKOXYAMINE (111-42-2)

LOAEL (dermal, rat/rabbit, 90 days)	32 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 411 (Subchronic Dermal Toxicity: 90-Day Study)
-------------------------------------	---

NOAEC (inhalation, rat, dust/mist/fume, 90 days)	0.003 mg/l air Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study)
--	--

STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.
------------------------	--

Aspiration hazard : Not classified

Additional information : Based on available data, the classification criteria are not met

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

SECTION 12: Ecological information

12.1. Toxicity

Ecology - water : Harmful to aquatic life with long lasting effects.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)	
LC50 - Fish [1]	10 – 100 mg/l

ALKOXYAMINE (111-42-2)	
EC50 - Crustacea [1]	30.1 mg/l Test organisms (species): Ceriodaphnia dubia
EC50 - Crustacea [2]	89.9 mg/l Test organisms (species): Ceriodaphnia dubia
EC50 72h - Algae [1]	9.5 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 72h - Algae [2]	2.7 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 96h - Algae [1]	9.7 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 96h - Algae [2]	2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
LOEC (chronic)	1.56 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC (chronic)	0.78 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC chronic fish	> 1 mg/l Test organisms (species): other: freshwater fish

ALKENYL ALKANOL AMIDE (68603-38-3)	
LC50 - Fish [1]	1460 mg/l
EC50 - Other aquatic organisms [1]	55 mg/l

12.2. Persistence and degradability

ULTRACUT EVO 255	
Persistence and degradability	May cause long-term adverse effects in the environment.

12.3. Bioaccumulative potential

ULTRACUT EVO 255	
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Ecology - waste materials : Avoid release to the environment.

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

ULTRACUT EVO 255

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:	
Acute Tox. 3 (Dermal)	Acute toxicity (dermal), Category 3
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
H302	Harmful if swallowed.
H311	Toxic in contact with skin.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.