



LCEDI

TE Internal #: 5-2023347-3

TE Internal Description: LCEDI UPPER SHELL WITH DATUM MARK
PLATED

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > LVDS Connectors (LCEDI)



Number of Positions: 40

Mated Height: 1.1 mm [.043 in]

LVDS Connector Product Type: Connector Shell

Features

Product Type Features

LVDS Connector Product Type	Connector Shell
-----------------------------	-----------------

Configuration Features

Number of Rows	1
Number of Positions	40

Body Features

Shell Base Material	Copper Alloy
---------------------	--------------

Housing Features

Centerline (Pitch)	.5 mm[.02 in]
--------------------	---------------

Dimensions

Mated Height	1.1 mm[.043 in]
--------------	-----------------

Industry Standards

Compatible With Approved Standards Products	VESA
---	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | LCEDI

LVDS Connectors (LCEDI)(6)

Customers Also Bought

TE Part #1770575-3
VAO ITEM, RJ45 W/LEDs, DIP TYPE

TE Part #66393-4
III+ PIN,30-26,30AU/FL,STRIP

TE Part #2023314-3
(LCEDI) SR interface plug conn 40pos

TE Part #1982295-4
ELCON MINI 2P RA HEADER,GOLD,W/O CODING



TE Part #1-1734580-3
MOD-Jack, RJ45, 10P10C, SHD LP, 30u" Au

TE Part #4-1775099-5
ATX PWR CONN 14 POS

TE Part #2023317-1
(LCEDI) SR serie plug upper shell 40pos

TE Part #2227644-3
HEAT SINK CLIP, QSFP28

TE Part #2023308-3
(LCEDI) SR interface Rec conn 40pos

TE Part #6274084-1
JACK ASSEMBLY, BNC

Documents

Product Drawings

LCEDI UPPER SHELL WITH DATUM MARK PLATED

English

CAD Files

Customer View Model

ENG_CVM_CVM_5-2023347-3_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2023347-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2023347-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773457-2_LCEDI/LCEDI_SR_QUICK_REFERENCE_GUIDE

English

Product Specifications

LCEDI CONNECTOR PRODUCT SPECIFICATION

Japanese

Product Specification

Japanese

