



Connectors &gt; D-Shaped Connectors

Number of Positions: **25**Connector & Housing Type: **Receptacle**Connector System: **Board-to-Board**Connector Mounting Type: **Board Mount**Connector Shell Size: **3**

## Features

### Product Type Features

Shell Material Configuration	Full Metal Shell
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector Shell Size	3
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Number of Positions	25
Number of Rows	2
PCB Mount Orientation	Vertical

### Body Features

Insert Material	Thermoplastic
Shell Plating Material	Tin
Primary Product Color	Black
Connector Profile	High

### Contact Features

Contact Thickness	30 µin
Contact Underplating Material	Palladium Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze

PCB Contact Termination Area Plating Material	Tin-Lead
Contact Shape & Form	Square
Contact Current Rating (Max)	6 A
Contact Options	Installed

#### Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]
Square Termination Post & Tail Dimension	.63 mm[.025 in]

#### Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Mating Retention	Without

#### Housing Features

Housing Material	Thermoplastic
Shell Material	Steel
Centerline (Pitch)	2.77 mm[.109 in]

#### Dimensions

PCB Thickness (Recommended)	1.57 – 2.36 mm[.062 – .093 in]
Row-to-Row Spacing	2.84 mm[.112 in]

#### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

#### Operation/Application

Circuit Application	Signal
---------------------	--------

#### Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

#### Packaging Features

Packaging Quantity	10
Packaging Method	Tube

## Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JUNE 2024 (241)</p> <p>SVHC &gt; Threshold:</p> <p>Pb (13% in Component Part)</p> <p><b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not lead free process capable

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | **AMPLIMITE HD-20**



D-Shaped Connectors(285)



PCB D-Sub Connectors(285)

## Customers Also Bought



TE Part #1-111196-1  
050 RCPT SYSTEM 50 30 DPLX



TE Part #9-146281-0  
40 MODII HDR SRST B/A .100CL



TE Part #640455-3  
03P MTA100 HDR ASSY SQ R/A POL




TE Part #3-644020-4  
04P MTA100 CONN ASSY 30AU



TE Part #5-1437657-7  
8PCV-02-006=#8 TRIBARRIER TERM




TE Part #3-1437664-0  
NC6-P108-02=NC6 ASSEMBLY




TE Part #1825140-2  
MGDH04STR04=1/2 PITCH LOW P  
DIP T&R



TE Part #1-2176326-6  
CRGP 0603 180R 1%  
DIP T&R



TE Part #5055557-4  
10 POWER TAP ASSY .100



TE Part #1-1825027-2  
FSMRA4JHA04=R/A, TACT PB SW, 260

## Documents

### Product Drawings

25 RCPT SP/MS STD

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_745187-1\\_P.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_745187-1\\_P.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_745187-1\\_P.2d\\_dxf.zip](#)

English

3D PDF

3D

3D PDF

English



Customer View Model

[ENG\\_CVM\\_745187-1\\_M.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_745187-1\\_M.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_745187-1\\_M.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

[Application Specification](#)

English