

Keysight Technologies

The Keysight Remote Link Solution



Why Go Wireless?



On site testing in large industrial sites can be challenging.



Machinery may be in operation.



Test points can be far apart, or high above the ground.


Have you ever wanted to carry out the tasks below with a handheld DMM but could not do so?

- Measure multiple points during troubleshooting and yet log all of the data simultaneously?
- Need to make measurements at electrical panels while toggling switches at the other end of the hall?
- Diagnose and evaluate live machinery from a safe distance?
- Monitor measurements in harsh environments?
- Log all of the data to diagnose intermittent issues from afar?

All these are made possible with the Keysight Remote Link Solution for Keysight U1200 Series and Keysight U1450A/60A Series handheld meters

Keysight lets you turn your iOS/Android smartphone or tablet into a remote measurement, control and reporting device.

The Remote Link Solution



The core of the solution is the Keysight U1177A/U1117A IR-to-*Bluetooth*® adapters, which is compact *Bluetooth* modules that plug into any compatible Keysight handheld meters.¹ The IR-to-*Bluetooth* adapters allow you to safely measure, view and log test measurements from a distance of up to 100 meters.² The solution also allows users to log and monitor data on a variety of display devices, including iOS/Android smart devices, Windows PCs, or the new U1115A remote logging display.



The new Keysight U1115A remote logging display allows users to view readings of up to four handheld meters simultaneously. The remote logging display comes with 60,000 points of interval logging memory, letting users store more test data for future review or analysis.



Note:

1. Refer to Table 1 for compatible Keysight handheld meters.
2. Refer to Table 2 for connectivity distance.


The Software Setup

The Keysight remote link solution comes with complimentary software applications, the Keysight Mobile Meter and Keysight Mobile Logger for iOS and Android smart devices.

First, download both applications from www.keysight.com/find/hhmeterapp or from the Google Play Store/Apple iTunes app store.


Keysight Mobile Meter Application (iOS/Android)

Monitor up to three measurements from three HH meters simultaneously




- 1) Use Voice-Out to have measurements read out so that you can fully concentrate on probing at the right points for greater safety
- 2) Shows the serial number of the connected multimeter and its battery status
- 3) Iconographic indicating the type of measurement function currently in use, replicating your DMM's display
- 4) Select desired type of measurement (voltage, current, resistance) and measure wirelessly from up to 10 meters away
- 5) Display measurements from up to three handheld meters
- 6) Freeze readings for your application/troubleshooting needs
- 7) Easily identify the HH DMM used for this measurement (Simply press the icon and the respective HH DMM will blink and the display of the HH DMM will blink)

- 8) Makes notes as you measure for your reference at a later time
- 9) Share data as text and/or a picture and send the file via email and sms




Keysight Mobile Logger Application (iOS/Android)




- 1) Monitor up to three measurements from three HH DMMs simultaneously
- 2) View real-time data trending for a particular HH DMM or the graphs for all three HH DMMs

- 3) Stop the data logging and zoom in on the trending graph to view details
- 4) Log data manually when the need arises



Keysight Insulation Tester Application (iOS/Android)



- 1) Enter a unique name or TestID for each test
- 2) Select type of test you want to perform, such as Spot test, Timed test, PI test, DAR test, Pass/Fail test, Earth Bond test and test data downloading from unit's memory
- 3) Primary measurement display
- 4) Measurement unit and function
- 5) Display the connected U1117A adapter
- 6) Properties View displays the test voltage, elapse time and resistance value
- 7) Start the insulation resistance testing
- 8) Stop the spot test
- 9) Enter remarks to the test report


- 10) Abort all the insulation resistance testing
- 11) Display the insulation test data in the table format
- 12) Zoom and View softkeys, designed for graph control
- 13) Display the logged data in graph view for trending purposes
- 14) Plot the insulation test data in graphical view as test in progress
- 15) Display, edit, export, backup and delete the list of automatic data logging sessions or manually logged data
- 16) Start/stop automatic data logging
- 17) Generate and export test report in PDF format via email or Dropbox
- 18) Tap to initiate single point manual data logging

The Keysight Handheld Meter Logger Software for Personal Computer (PC) Users

Alternatively, data logging and monitoring activities can also be performed with Keysight Handheld Meter Logger software via *Bluetooth* connection.



View up to 10 handheld meters' readings or trending with Keysight Handheld Meter Logger



View insulation resistance test trends and generate test reports on a PC

Notes:

1. Tested on certain iOS/Android smart phones and tablets.
Please refer to www.keysight.com/find/U1117A for more information.
2. Measurement functions depend on the rotary position of the HH meter.
3. Number of HH meter connections depends on the smart phone/tablet used.

For more information, visit www.keysight.com/find/hhgowireless

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.



www.axiestandard.org

AdvancedTCA® Extensions for Instrumentation and Test (AXIe) is an open standard that extends the AdvancedTCA for general purpose and semiconductor test. Keysight is a founding member of the AXIe consortium. ATCA®, AdvancedTCA®, and the ATCA logo are registered US trademarks of the PCI Industrial Computer Manufacturers Group.



www.lxistandard.org

LAN eXtensions for Instruments puts the power of Ethernet and the Web inside your test systems. Keysight is a founding member of the LXI consortium.



www.pxisa.org

PCI eXtensions for Instrumentation (PXI) modular instrumentation delivers a rugged, PC-based high-performance measurement and automation system.



www.keysight.com/go/quality

Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2008
Quality Management System

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

Bluetooth and the Bluetooth logos are trademarks owned by Bluetooth SIG, Inc., U.S.A. and licensed to Keysight Technologies, Inc

www.keysight.com/find/hhgowireless

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
(BP-09-23-14)