



Technical data

16015C3

Single row deep groove ball bearings

Deep groove ball bearing, radial contact, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	75 mm
D - External diameter	115 mm
B - Bearing/Inner ring width	13 mm
rs - Min fillet radius	0,6 mm
Radial clearance class	C3
Mass	0,464 kg

PRODUCT PERFORMANCE

C - Dynamic load	27600000 mN
C0 - Static load	24000000 mN
Cu - Fatigue limit load	1600000 mN
f0 - Coefficient	16.6
N lim - Oil lubrication limit speed	40200 °/s
N lim - Grease lubrication limit speed	34200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	79 mm
Da max - Max shoulder diameter OR	111 mm
ra max - Max shaft & housing fillet radius	0,6 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.Fr + Y.Fa$$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$$Po = X_0.Fr + Y_0.Fa$$

X ₀	Y ₀
0.6	0.5

For single or DT bearing arrangement :

If Po ≤Fr, then use Po = Fr