

Product data sheet

Specifications



Repacked, safety transformer, Acti9 iTR, 230VAC, 40VA, 12V to 24V output

A9A15220W



This repacked option saves 22.314 over the standard condition

Main

Transformer type	Safety transformer
Range	Acti9
Range of product	Acti9
Product name	Acti9 iTR
Product or component type	Transformer
Device short name	iTR

Complementary

[Ue] rated operational voltage	230 V AC 50 Hz
Output voltage	12/24 V: +/-5 % on load 14/28 V: off load
Output short-circuit protection	Built-in
rated power in VA	40 VA
Temperature derating table	40 VA 35 °C 38 VA 40 °C 32 VA 50 °C 24 VA 55 °C 18 VA 60 °C
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	10
Height	89 mm
Width	90 mm
Depth	60 mm
Colour	White
Auxiliary connection terminal	Tunnel type terminals 4 mm ²
Wire stripping length	5 mm
Tightening torque	0.5 N.m

Environment

Standards	EN 60742 EN 61558-2-6 IEC 61558-2-6
Product certifications	NF
Overvoltage category	Class II with terminal shields in option

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.600 cm
Package 1 Width	11.000 cm
Package 1 Length	11.500 cm
Package 1 Weight	1.186 kg
Unit Type of Package 2	S01
Number of Units in Package 2	3
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.746 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

22 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

6edbd8bf-8086-4f8e-a012-80f9e4a1db80

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins