

Eaton 135727

Catalog Number: 135727

Eaton Moeller® series E65 Diffuse reflective sensor, Sn=200mm, 4L, 10-30VDC, dark, NPN, PNP, quad 40, insulated material, M12 E65-SMSD200-HDD

General specifications



Product Name	Catalog Number
Eaton Moeller® series E65 Diffuse reflective sensor	135727
	EAN
	4015081325207
Product Length/Depth	Product Height
139.7 mm	139.7 mm
Product Width	Product Weight
38.1 mm	0.11 kg
Certifications	Catalog Notes
UL Category Control No.: NRKH, NRKH7 Yellow	

CSA File No.: UL report applies to both
US and Canada
Certified by UL for use in Canada
CE
CSA-C22.2 No. 14
UL
UL File No.: E166051
IEC/EN 60947-5-2
UL 508

Product specifications

Type

Optical sensors

Electric connection type

Connector M12

Enclosure material

Plastic

Enclosure type

Cuboid

Operating mode

Switching principle: Dark switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Protection against polarity reversal

Reflected-light beam

Short-circuit protection

Protection against wire breakage

Voltage type

DC

Wire size

0

Connection type

Plug-in connection M12 x 1

4-wire

Cable sheath material

Other

Light type

Polarity free red light

Degree of protection

IP68

NEMA 6P, 13

Interface type

Other

LED indicator

Resources

Catalogs

[Product Range Catalog Sensors](#) – products, basic information, applications

Declarations of conformity

[DA-DC-00004657.pdf](#)

[DA-DC-00004652.pdf](#)

Drawings

[eaton-proximity-switches-dimensions-012.eps](#)

[eaton-proximity-switches-e65-diffuse-reflective-sensor-dimensions.eps](#)

[eaton-proximity-switches-3d-drawing.eps](#)

Installation instructions

[IL05305004Z](#)

mCAD model

[DA-CD-90_28290_012](#)

[DA-CS-90_28290_012](#)

Status indication of Switching state: Red LED

Status indication of Operating voltage: Green LED

Switch function type

Other

Load current

Max. 100 mA (I_e)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

50 g, Mechanical, Shock duration 10 ms

Optical surface material

Plastic

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at DC - max

30 V

Rated control supply voltage (U_s) at DC - min

10 V

Rated switching distance (S_n)

200 mm

Reflector distance - min

0 mm

Sensor height

55 mm

Sensor length

41 mm

Switching distance - max

200 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Dark switching

Switching output type

NPN

Sensor material

Insulated material

Wavelength of the sensor

660 nm

Width sensor

33 mm

Product category

E65 SM Series

Response time

1 ms

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-25 °C

Diameter sensor

0 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Operating temperature - max

55 °C

Operating temperature - min

-25 °C

Operational current (Ib) in the switched state at 24 V DC

20 A

Adjustment type

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia