



PRODUCT-DETAILS

# XT1B 160 TMD 25-450 3p F F

## XT1B 160 TMD 25-450 3p F F



General Information	
Extended Product Type	XT1B 160 TMD 25-450 3p F F
Product ID	1SDA066801R1
EAN	8015644003289
Catalog Description	XT1B 160 TMD 25-450 3p F F
Long Description	C.BREAKER TMAX XT1B 160 FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMD R 25-450 A

ABB EcoSolutions	
ABB EcoSolutions	Yes
ABB Site Meeting Group Waste To Landfill Target	UL 2799 Zero Waste To Landfill Validation available
End Of Life Disassembling Instructions	9AKK108468A2347
Environmental Product Declaration - EPD	9AKK108468A1890 9AKK108468A7793
Extended Product Lifetime	Product Modularity

Recyclability Rate of the Product acc. to EN45555

Design for Closing Resource Loops - Standard EN45555 - 55.9 %

### Material Compliance

REACH Declaration	9AKK108466A1425
RoHS Declaration	9AKK108466A1424
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
Toxic Substances Control Act - TSCA	9AKK108467A8326
SCIP	8acd1baa-b059-4d51-abdc- <a href="#">ea46defeb35e</a> Italy
Simplified SCIP	<a href="#">d1aaf08d-e25f-4668-a057-4628057c8769</a> Germany <a href="#">a3cb6bff-8410-4229-8646-6cccf9434c2</a> Poland <a href="#">9ff0f6b4-a69c-43a0-ba19-92bc124a3464</a> Norway <a href="#">2b859db5-b8d7-4582-9f9e-a714dfb57603</a> Finland <a href="#">2c089ba4-fd3a-4e3d-b3da-8607a803d823</a> Netherlands <a href="#">d265c6de-5560-448d-be55-8b6e38c8e47e</a> Germany <a href="#">e0d795ac-e812-48bb-93ae-39c2b1fe2aa8</a> Denmark <a href="#">b9b12f17-54ef-40cc-8b89-a4e1a85e6f16</a> Germany <a href="#">c6298b97-9d9e-42ed-b595-bc5572008f7f</a> Croatia <a href="#">49905c59-d051-4933-ae8-957313e7c76b</a> France <a href="#">49a55cdf-4a0f-48db-a710-1f0b682d75da</a> Sweden <a href="#">ba601371-442d-4856-91e4-aed91c4397a6</a> Germany <a href="#">96e8b14b-e8c2-4ff3-b457-9d321b80a48c</a> Germany <a href="#">f834e079-b952-4094-819d-77fa6c5c2e9f</a> France <a href="#">ef2515cc-3f80-4037-9726-465563cd6237</a> Netherlands <a href="#">755304cd-f665-4b13-9cf6-10f93e474874</a> Spain <a href="#">efe35e1a-4e77-4211-bebc-18b4ca05a992</a> Estonia <a href="#">c6675afb-be78-4a8f-9a37-e2fbbce32849</a> Greece <a href="#">f105555f-afc7-4bfc-8428-6db856df2c98</a> Portugal <a href="#">243cc790-2e64-4328-97df-dd54d53fbc3</a> Bulgaria <a href="#">f8571fb3-a76a-45f5-b32b-a8fb8bc01539</a> Sweden <a href="#">0f189183-bc01-4cac-acea-7637fb6a169a</a> Poland <a href="#">dbf95c07-c982-4c67-8a65-b5087833b881</a> Netherlands <a href="#">f099941a-3638-4e46-bc58-30dd8b7335ab</a> Czech Republic <a href="#">29ca709b-7996-405d-bd6d-5d766c178307</a> Poland <a href="#">8a2dc3a6-691e-442a-b562-b5f3081e360d</a> Netherlands <a href="#">ed75ce49-731b-4a2c-a2aa-48b67198a8ec</a> Netherlands

### Environmental

Environmental Information	9AKK108467A6707
---------------------------	-----------------

### Ordering

Order Code US and Canada	XT1BE3025AFF000XXX
E-Number (Finland)	3640497
E-Number (Norway)	4309602
EAN	8015644003289
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

### Dimensions

Product Net Width	76.2 mm
Product Net Height	130 mm
Product Net Depth / Length	70 mm
Product Net Weight	1.1 kg

### Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	128 mm
Package Level 1 Height	135 mm
Package Level 1 Depth / Length	143 mm
Package Level 1 Gross Weight	1.126 kg
Package Level 1 EAN	8015644003289

### Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Automatic Circuit Breaker
Version	F
CAD Dimensional Drawing	1SDH001295R0008

### Technical

Connecting Capacity Main Circuit	Busbar 45.5 ... 80 mm <sup>2</sup>
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	240 cycles per hour 25000 cycle
Number of Poles	3P
Opening Time	CB with SOR 30 ms CB with UVR 30 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 2 W
Rated Current (I <sub>n</sub> )	25 A
Rated Frequency (f)	50 / 60 Hz
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	8 kV
Rated Instantaneous Short-Circuit Current Setting (I <sub>i</sub> )	450 A
Rated Insulation Voltage (U <sub>i</sub> )	800 V
Rated Operational Voltage	690 V AC 500 V DC
Rated Service Short-Circuit Breaking	(220 V AC) 25 kA (230 V AC) 25 kA

Capacity (I <sub>cs</sub> )	(240 V AC) 25 kA (380 V AC) 18 kA (415 V AC) 18 kA (440 V AC) 11.25 kA (500 V AC) 8 kA (525 V AC) 6 kA (690 V AC) 3 kA (250 V DC) 2 Poles in Series 18 kA (500 V DC) 3 Poles in Series 18 kA
Rated Ultimate Short-Circuit Breaking Capacity (I <sub>cu</sub> )	(220 V AC) 25 kA (230 V AC) 25 kA (240 V AC) 25 kA (380 V AC) 18 kA (415 V AC) 18 kA (440 V AC) 15 kA (500 V AC) 8 kA (525 V AC) 6 kA (690 V AC) 3 kA (250 V DC) 2 Poles in Series 18 kA (500 V DC) 3 Poles in Series 18 kA
Rated Uninterrupted Current (I <sub>u</sub> )	160 A
Rated Voltage (U <sub>r</sub> )	690 V
Recommended Screw Driver	Main Circuit M6
Release	TMD
Release Type	TM
Setting Range	17.5...25 A
Short-Circuit Performance Level	B
Standards	IEC60947-2
Sub-type	XT1
Terminal Connection Type	Front
Terminal Type	Bolt
Tightening Torque	6 N·m

### Certificates and Declarations

ATEX Certificate	No certification needed
Data Sheet, Technical Information	1SDC210100D0206 1SDC210099D0206
Declaration of Conformity - CE	9AKK106713A5532
GL Certificate	1SDL000163R0103
LR Certificate	1SDL000163R0100
UL Certificate	No certification needed
VDE Certificate	No certification needed
Dimension Diagram	1SDH000719R0100
Mechanical Drawings	1SDH000719R0100
Wiring Diagram	1SDM000068R0001
Instructions and Manuals	1SDH000719R0001

### External Classifications and Standards

ETIM 9	EC000228 - Power circuit-breaker for trafo/generator/installation protection
ETIM 10	EC000228 - Power circuit-breaker for trafo/generator/installation protection

Object Classification Code	Q
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27370409

---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

