



CUT PROTECTION

COLD PROTECTION



# RADIUS EW151

## CUT RESISTANT, THERMAL, WATER REPELLENT FULLY COATED LATEX GLOVE

A fully coated glove combining thermal properties and cut resistance with an open cuff for easy donning and doffing. Ideal for sharp handling in cold and wet environments.

### FEATURES

- › Cut resistant: Level D (EN 388:2016)
- › Cut resistant liner protects against sharp parts and the thermal liner provides insulation at cold temperatures
- › Flexible and robust glove offering a good level of dexterity
- › Water repellent for working in wet environments
- › Protects the hand from liquids with optimal long lasting grip
- › Open cuff (cut-out in wrist area) to ease removal of the glove
- › No irritation by seams in contact with the skin



### SUITABLE FOR


#### Typical Industries

- Construction
- Glass
- Public Works
- Transportation
- Waste Management

#### Suitable Applications

- Sharp and Wet Parts Handling
- Scaffolding

### CERTIFICATION



See overleaf for explanation





CUT PROTECTION

COLD PROTECTION



# RADIUS EW151

## SUITABLE FOR

MATERIALS	LINER:	13gg HPPE, glass, nylon, acrylic
	COATING:	Double coated crinkle latex over latex
COLOUR	Grey/Black	
LENGTH (mm)	220-270 (Size Dependent)	
CUFF STYLE	Knitted	

## ORDERING DETAILS

SIZE	CODE	PACKAGING
7/S	SKY00131	10 pairs per bag
8/M	SKY00132	60 pairs per case
9/L	SKY00133	
10/XL	SKY00134	
11/XXL	SKY00135	

## RECOMMENDATIONS FOR USE


- CLEANING / MAINTENANCE** Both new and used gloves should be thoroughly inspected before being worn to ensure no damage is present. If any damage is found on the gloves they should be disposed of. Gloves should not be left in contaminated condition if reuse is intended in which case gloves should be cleaned as far as possible. To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown.
- STORAGE** Ideally stored in dry conditions between 10°C and 30°C in the original packaging and sheltered from direct light. Do not exceed 40°C.
- OBSOLESCENCE** When stored as recommended, the gloves will not suffer a change in mechanical properties for up to three years from the date of manufacture. Service life cannot be specified and depends on the application and it is the responsibility of user to ascertain suitability of the glove for its intended use.
- GENERAL** None of the materials or processes used in the manufacture of these products is known to be harmful to the wearer. If reaction was to occur, then obtain medical assistance.
- CAUTION!** Avoid using near moving machinery due to entanglement hazard.
- PLEASE NOTE** The results of the physical tests should help in glove selection, however it must be understood that actual conditions of use cannot be simulated and it is the responsibility of the end user and not the manufacturer to determine glove suitability for the intended use.

## CERTIFICATION LEGENDS



MECHANICAL HAZARDS  
EN 388: 2016

### PERFORMANCE LEVELS\*




\* If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



COLD HAZARDS  
EN 511

### PERFORMANCE LEVELS



## ABOUT GLOBUS

World leader in protecting hands, Globus serves organisations with bespoke hand protection solutions built from a professional range of high performance protective gloves.

Globus is proud to offer bespoke solutions that deliver robust commercial benefits not just safety improvements. We have an enviable track record in helping to reduce hand accident rates whilst delivering improved comfort and productivity as well as waste and cost reductions.

Globus applies its expertise across a spectrum of industries, meeting and exceeding a diverse range of hand protection requirements; from the rigorous demands of the petrochemical and construction industries to the complexities of clean room and aerospace manufacturing.

Find out why leading companies rely on a solution from Globus to help implement a comprehensive hand protection policy. Contact us today.

### EUROPE

[www.globus.co.uk](http://www.globus.co.uk)

E: [sales@globus.co.uk](mailto:sales@globus.co.uk)

T: +44 (0)161 877 4747

F: +44 (0)161 877 4746

### MIDDLE EAST AND AFRICA

[www.globusgroup.com/gcc](http://www.globusgroup.com/gcc)

E: [gcc@globusgroup.com](mailto:gcc@globusgroup.com)

T: +971 4 882 9962

F: +971 4 882 9963



Globus (Shetland) Ltd, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM  
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

© 2019 Globus (Shetland) Ltd | SKY-DATA-RAD\_EW151-0219\_1