



Burrs TC 6 x 12.7mm set - 5 pc

CARBIDE BURRS

- According to DIN 8033.
- Double cut tothing geometry ensures excellent material removal, low vibrations for easier handling and smaller swarfs.
- Suitable for unhardened and hardened steel, cast iron and non ferrous metals (aluminium, brass, copper).
- Includes: Types B, C, D, H, M.
- Type B: End cut cylinder for top and side cutting.
- Type C: Cylindrical ball nose for top and side cutting.
- Type D: Ball for milling holes and creating concave cuts.
- Type H: Flame for contouring.
- Type M: Cone for angled edges and narrow contours.



Article Number	4932493576
Pack quantity	5
Shank Diameter (mm)	6
Width (mm)	12.7