



SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Issue date: 19/06/2020 Revision date: 11/02/2021 Version: 7.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : SAPPHIRE Hi-Torque Range

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : For professional use only
Industrial
Use of the substance/mixture : Lubricants, Greases and Release Products

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Signal word (CLP) : -
Hazard statements (CLP) : H412 - Harmful to aquatic life with long lasting effects.

2.3. Other hazards

No additional information available

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
amines, coco alkyl	(CAS-No.) 61788-46-3 (EC-No.) 262-977-1 (EC Index-No.) 612-285-00-4 (REACH-no) 01-2119473798-17	0.1 – 1	Acute Tox. 4 (Oral), H302 Skin Corr. 1B, H314 Eye Dam. 1, H318 STOT SE 3, H335 STOT RE 2, H373 Asp. Tox. 1, H304 Aquatic Acute 1, H400 (M=10) Aquatic Chronic 1, H410 (M=10)

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice.
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: Not expected to present a significant hazard under anticipated conditions of normal use.
------------------	--------------------------------------------------------------------------------------------

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.
Collect spillage.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

Hygiene measures : Always wash hands after handling the product. Do not eat, drink or smoke when using this product. Separate working clothes from town clothes. Launder separately.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in original container. Keep container closed when not in use.

Incompatible products : Strong bases. Strong acids.

Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:

Chemical goggles or safety glasses

8.2.2.2. Skin protection

Hand protection:

Wear protective gloves. Nitrile rubber gloves

8.2.2.3. Respiratory protection

Respiratory protection:

Not required for normal conditions of use

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Blue.
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: > 300 °C
Flash point	: > 240 °C
Auto-ignition temperature	: > 240 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: ≈ 0.89
Solubility	: insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: 150 – 680 mm ² /s
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

9.2. Other information

VOC content : 0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Stable under normal conditions of use.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met

amines, coco alkyl (61788-46-3)

STOT-single exposure	May cause respiratory irritation.
----------------------	-----------------------------------

STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

amines, coco alkyl (61788-46-3)	
STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.

Aspiration hazard : Not classified
Additional information : Based on available data, the classification criteria are not met

SAPPHIRE Hi-Torque Range	
Viscosity, kinematic	150 – 680 mm ² /s

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.

12.2. Persistence and degradability

SAPPHIRE Hi-Torque Range	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

SAPPHIRE Hi-Torque Range	
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.
Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 0 g/l

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

SAPPHIRE Hi-Torque Range

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Full text of H- and EUH-statements:	
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Asp. Tox. 1	Aspiration hazard, Category 1
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
STOT RE 2	Specific target organ toxicity — Repeated exposure, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H302	Harmful if swallowed.
H304	May be fatal if swallowed and enters airways.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H335	May cause respiratory irritation.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.