

# Product datasheet

Specifications



Floor standing polyester enclosure,  
PanelSeT PLA, open bottom,  
ventilated canopy,  
1000x1000x420mm, IP44, IK10

NSYPLAZT10104G

EAN Code: 3606480775963

Price: 1.420,00 EUR

## Main

|                           |                                                                                              |
|---------------------------|----------------------------------------------------------------------------------------------|
| Range                     | PanelSeT                                                                                     |
| product name              | PanelSeT PLA                                                                                 |
| Enclosure type            | Multi-purpose                                                                                |
| Product or component type | Suitable enclosure                                                                           |
| Version                   | PLAZT                                                                                        |
| Nominal height            | 1000 mm                                                                                      |
| Nominal width             | 1000 mm                                                                                      |
| Nominal depth             | 420 mm                                                                                       |
| Enclosure mounting        | Floor-standing                                                                               |
| Device composition        | 1 top part<br>1 bottom part<br>2 side part<br>2 door<br>2 rear panel<br>1 canopy<br>1 plinth |

## Complementary

|                             |                                                                            |
|-----------------------------|----------------------------------------------------------------------------|
| Body type                   | Open top and bottom part assembled with side parts                         |
| Door type                   | Plain front                                                                |
| Number of doors             | 2 door(s)                                                                  |
| Door opening side           | Right and left (180 °)                                                     |
| Lock type                   | 4 points lock, handle with 5 mm double bar insert                          |
| Accessibility for operation | Rear<br>Front<br>Top<br>Bottom                                             |
| Removable parts             | Door by hinges<br>Rear panel by fixing element<br>Canopy by fixing element |
| Material                    | Polyester reinforced with fibreglass                                       |
| Colour                      | Grey (RAL 7035)                                                            |
| Standards                   | IEC 62208                                                                  |
| Product certifications      | Veritas                                                                    |
| Electrical insulation class | Class II                                                                   |

Rates duty January 2016

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Environment

|                                     |                                                                                        |
|-------------------------------------|----------------------------------------------------------------------------------------|
| IP degree of protection             | IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy) |
| IK degree of protection             | IK10 conforming to IEC 62262 (plain door)                                              |
| Fire resistance                     | 960 °C conforming to IEC 62208                                                         |
| Ambient air temperature for storage | -35...90 °C                                                                            |

# Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 45.000 cm  |
| Package 1 Width              | 103.500 cm |
| Package 1 Length             | 110.500 cm |
| Package 1 Weight             | 47.400 kg  |
| Unit Type of Package 2       | PAM        |
| Number of Units in Package 2 | 2          |
| Package 2 Height             | 123.000 cm |
| Package 2 Width              | 100.000 cm |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 109.400 kg |

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint                               |                                               |
|-------------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 369                                           |
| Environmental Disclosure                              | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                                            |
|----------------------------------------|------------------------------------------------------------|
| Packaging made with recycled cardboard | No                                                         |
| Packaging without single use plastic   | No                                                         |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number                            | 1341ad4e-77b9-40e3-bab0-32043fbc5959                       |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                          |

Use Again

| Repack and remanufacture |                                          |
|--------------------------|------------------------------------------|
| Circularity Profile      | No need of specific recycling operations |
| Take-back                | No                                       |