





flow control regulators – polymer version

7640-7649 "miniature" swivel outlet





Ø	D	C	adjustment on outlet	adjustment on inlet	F	H mini	H maxi	H1	L	Δkg
4	M5x0,8	7640 04 19			10	27	31	19,5	16,5	0,011

7740 "compact", "swivel outlet", BSP parallel





Ø	D	C		F	H mini	H maxi	H1	L	Δkg
4	G1/8	7740 04 10		14	32,5	36,5	19,5	16,5	0,030
6	G1/8	7740 06 10		14	44,5	49,5	22,5	22	0,028
6	G1/4	7740 06 13		17	45	50	22,5	22	0,032
8	G1/8	7740 08 10		17	49	55,5	24,5	26,5	0,042
8	G1/4	7740 08 13		17	49	55,5	24,5	26,5	0,042
10	G3/8	7740 10 17		22	57,5	66	30,5	34	0,097
12	G1/2	7740 12 21		27	63,5	74	32	39	0,148

7010 "compact", with recessed adjustment screw, "exhaust" version, BSP parallel and metric





Ø	D	C		E	F	H	L	L1	Δkg
4	M5x0,8	7010 04 19		4	8	17,5	18,5	5	0,007
4	G1/8	7010 04 10		5	13	25	19	7	0,017
6	M5x0,8	7010 06 19 *		4	8	17,5	19	5	0,017
6	G1/8	7010 06 10		5	13	25	21	7	0,019
6	G1/4	7010 06 13		8	17	26,5	22	9,5	0,034
8	G1/8	7010 08 10		5	13	25	26	7	0,020
8	G1/4	7010 08 13		8	17	26,5	27	9,5	0,035
8	G3/8	7010 08 17		7,5	20	37,5	29	11,2	0,042
10	G1/4	7010 10 13		8	17	26,5	29	9,5	0,038
10	G3/8	7010 10 17		7,5	20	37,5	31	11,2	0,043
12	G3/8	7010 12 17		7,5	20	37,5	34,5	11,2	0,045

7011 "compact", with recessed adjustment screw, "supply" version, BSP parallel and metric



Ø	D	C		E	F	H	L	L1	Δkg
4	M5x0,8	7011 04 19		4	8	17,5	18,5	5	0,007
4	G1/8	7011 04 10		5	13	25	19	7	0,017
6	M5x0,8	7011 06 19		4	8	17,5	19	5	0,017
6	G1/8	7011 06 10		5	13	25	21	7	0,019
6	G1/4	7011 06 13		8	17	26,5	22	9,5	0,034
8	G1/8	7011 08 10		5	13	25	26	7	0,020
8	G1/4	7011 08 13		8	17	26,5	27	9,5	0,035
8	G3/8	7011 08 17		7,5	20	37,5	29	11,2	0,042
10	G1/4	7011 10 13		8	17	26,5	29	9,5	0,038
10	G3/8	7011 10 17		7,5	20	37,5	31	11,2	0,043

7012 with recessed adjustment screw, bi-directional



Ø	D	C		E	F	H	L	L1	Δkg
4	M5x0,8	7012 04 19		4	8	17,5	18,5	5	0,007