

# M18 FHIW2P12-502X

## M18 FUEL™ 1/2" HIGH TORQUE IMPACT WRENCH WITH PIN DETENT

- Great power density: the M18 FUEL™ high torque impact wrench delivers 1220 Nm fastening torque and 1491 Nm of nut-busting torque in a compact size of 185 mm, which gives more access in tight spaces
- 2000 RPMs of no load speed to perform your task 35% faster than with the previous gen
- Our battery isolation system provides a secure battery connection and controls vibration transmitted to the pack
- Robust gearcase for more durability
- Tri-LEDs deliver high-definition lighting to increase workspace visibility
- 4-Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility
- Mode 4 bolt removal, provides maximum nut-busting torque then shifts to 750 rpm for outstanding control when removing fasteners
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



### REDLITHIUM™

|                                      |   |
|--------------------------------------|---|
| No load speed (rpm)                  | 0-700/ 0-1300/ 0-2000/ 0-2000                       |
| Impact rate (ipm)                    | 0-1400/ 0-2500/ 0-2700/ 0-2700                      |
| Max. torque (Nm)                     |   |
| Nut-busting torque (Nm)              | 1491  |
| Weight with battery pack (EPTA) (kg) | 3.4 (M18 B5)  |
| Kit included                         | 2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box |
| Article Number                       | 4933492786  |

