



ZMVV.E250316

Wire Connectors and Soldering Lugs

[Page Bottom](#)

Wire Connectors and Soldering Lugs

[See General Information for Wire Connectors and Soldering Lugs](#)

GUSTAV KLAUKE GMBH
AUF DEM KNAPP 46
42855 REMSCHEID, GERMANY

E250316

Pressure cable connectors, butt-type, "L Series", Model(s) LV0.75, LV1.5, LV10, LV120, LV150, LV16, LV185, LV2.5, LV240, LV25, LV300, LV35, LV4, LV400, LV50, LV500, LV6, LV630, LV70, LV95

Pressure cable connectors, butt-type, "R Series", Model(s) 17R, 18R, 19R, 20R, 21R, 22R, 23R, 24R, 25R, 26R, 27R, 28R, 29R, 30R, 31R, 32R, 33R, 34R

Pressure cable connectors, cross connectors, "L Series", Model(s) KVL1.5, KVL10, KVL120, KVL150, KVL16, KVL185, KVL2.5, KVL240, KVL25, KVL35, KVL4, KVL50, KVL6, KVL70, KVL95

Pressure cable connectors, cross-connectors, "R Series", Model(s) KV1.5, KV10, KV120, KV150, KV16, KV185, KV2.5, KV240, KV25, KV35, KV4, KV50, KV6, KV70, KV95

Pressure cable connectors, T-connectors, "L Series", Model(s) TVL1.5, TVL10, TVL120, TVL150, TVL16, TVL185, TVL2.5, TVL240, TVL25, TVL35, TVL4, TVL50, TVL6, TVL70, TVL95

Pressure cable connectors, T-connectors, "R Series", Model(s) TV1.5, TV10, TV120, TV150, TV16, TV185, TV2.5, TV240, TV25, TV35, TV4, TV50, TV6, TV70, TV95

Pressure terminal connectors, narrow palm type, "R Series", Model(s) 5SG, 6SG, 7SG, 8SG, 9SG, 10SG, 11SG, 12SG, or 13SG, followed by /1 or 2-digit number.

Pressure terminal connectors, angled-45 degree, "R Series", Model(s) 41R, 42R, 43R, 44R, 45R, 46R, 47R, 48R, 49R, 50R, 51R, 52R, 53R, or 54R, followed by a /1 or /2-digit number, and by Suffix -45.

Pressure terminal connectors, angled-45 degrees, "L Series", Model(s) L6, L10, L16, L25, L35, L50, L70, L95, L120, L150, L185, L240, L300, L400, followed by a /1 or /2-digit number, and by suffix -45.

Pressure terminal connectors, angled-90 degree, "R Series", Model(s) 41R, 42R, 43R, 44R, 45R, 46R, 47R, 48R, 49R, 50R, 51R, 52R, 53R or 54R, followed by a /1 or /2-digit number.

Pressure terminal connectors, angled-90 degrees, "L Series", Model(s) L6, L10, L16, L25, L35, L50, L70, L95, L120, L150, L185, L240, L300, L400, followed by a /1 or /2-digit number, and by suffix -90.

Pressure terminal connectors, fork type, "R Series", Model(s) 91C, 92C, 93C, 94C, 95C, 96C, or 97C, followed by a 1-digit number.

Pressure terminal connectors, straight, "L Series", Model(s) L0.75, L1.5, L2.5, L4, L6, L10, L16, L25, L35, L50, L70, L95, L120, L150, L185, L240, L300, L400, L500 or L630, followed by a 1 or 2-digit number, and by suffix MS.

Pressure terminal connectors, straight, "R Series", Model(s) 1R, 2R, 3R, 4R, 5R, 6R, 7R, 8R, 9R, 10R, 11R, 12R, 13R, or 14R, followed by /1 or 2-digit number., 91R, 92R, 93R, 94R, 95R followed by /3, /4, /5, or /6.

Note - All models may be suffixed with bk.

[Last Updated](#) on 2010-12-17

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2010 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2010 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

