

Technical data


1206SC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	30 mm
D - External diameter	62 mm
B - Bearing/Inner ring width	16 mm
rs - Min fillet radius	1 mm
Radial clearance class	C3
Precision class	P0
Mass	0,22 kg

PRODUCT PERFORMANCE

C - Dynamic load	15800000 mN
C0 - Static load	4650000 mN
Cu - Fatigue limit load	190000 mN
e - Coefficient	0.25
Y0 - Static axial load coefficient	2.6
Y1 - Lower axial load coefficient	2.5
Y2 - Upper axial load coefficient	3.9
N lim - Oil lubrication limit speed	72000 °/s
N lim - Grease lubrication limit speed	60000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	35 mm
Da max - Max shoulder diameter OR	57 mm



1206SC3
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm