

Features


- Stainless steel fittings are highly resistant to corrosion, making them suitable for use in various environments, including those exposed to moisture, chemicals, and harsh weather conditions
- They offer robustness and reliability, allowing them to withstand heavy loads, pressure, and mechanical stress, making them suitable for demanding applications across industries like construction, manufacturing, and plumbing
- Stainless steel fittings possess hygienic qualities, making them ideal for applications in industries



Specification

Material	Stainless Steel
Medium	Air, Steam, Water
Operating Pressure	-100 KPa ~ 1.2 MPa
Burst Pressure	3 MPa
Ambient Temperature	- 5 °C ~ - 200 ° C
Sealing Material	FKM
Thread	BSPT

Product Range & Drawing



Part Number	B (mm)	øC (mm)	øD (mm)	E (mm)	F (mm)	R、N	L2 (mm)	L1 (mm)	L (mm)
RND 425-00254	8	11	6	16.4	S12	R 1/8	21	21.1	42.2
RND 425-00255	11	11	6	16.4	S14	R 1/4	25	21.1	42.2
RND 425-00256	11	11	6	16.4	S17	R 3/8	25	21.1	42.2
RND 425-00257	14.5	11	6	16.5	S22	R 1/2	28.5	21.1	42.4
RND 425-00258	11	13.7	8	16.8	S14	R 1/4	27.4	22	44
RND 425-00259	11	13.7	8	16.8	S17	R 3/8	27.9	22	44
RND 425-00260	14.5	13.7	8	16.8	S22	R 1/2	31.4	22	44
RND 425-00261	11	15.5	10	18.4	S14	R 1/4	28.5	24.6	49.2
RND 425-00262	11	15.5	10	18.4	S17	R 3/8	29	24.6	49.2