

3M™ Overhead Projector

Model 2660

Get Up and Go Technology for People on the Go

Small but powerful, this 11-pound feature-packed overhead projector has three lenses for one of the sharpest images on the market. 2500 lumens of brightness and a varifocal lens feature ensure crispness and clarity. And, a handy lamp-changing feature means you'll never have to fumble around in the dark to replace a bulb. With the flip of a switch, you're back in business!



KEY FEATURES

- > Open triplet projection head - three lenses for the sharpest image technology on the market
- > Varifocal feature for precise focus
- > Lamp changer feature for instant bulb replacement
- > Easy-to-access controls
- > Convenient folding post for easy storage

ORDER NUMBER: X0-0038-0303-8

TECHNICAL SPECIFICATIONS

Specifications subject to change.

OPTICAL PERFORMANCE

- > Head: **open triplet, varifocal lens**
- > Illumination: **2,500 lumens ANSI**
- > Stage aperture: **286 mm x 286 mm** (11.25 inches x 11.25 inches)

LAMP DESCRIPTION

- > **Lamp ejector**
- > **Lamp changer**
- > Lamp Type: **FNT** (24 volts, 275 watts)
- > Lamp Life: **50** hours

PHYSICAL CHARACTERISTICS

- > Weight: **11** lbs.

ELECTRICAL FEATURES

- > Power-cord length: **3 m** (10 feet)

MECHANICAL

- > **Lamp interrupt switch:** Shuts off power to lamp when changing to prevent premature failure.
- > **Thermal protection circuit:** Cuts power to the lamp if the projector exceeds safe operating temperature.

**Ask
about 3M
LAMPS!**

1.800.328.1371

www.3M.com/meetings

"Wherever there's a great meeting, you'll find 3M."™

Visual Systems Division
Building A145-5N-01
6801 River Place Blvd.
Austin, TX 78726-9000

3M Canada
P.O. Box 5757
London, Ontario, Canada
N6A 4T1

3M Mexico, S.A. de C.V.
Apartado Postal 14-139
Mexico, D.F. 07070
Mexico

3M Presentation Solutions